

IRWIN®

New Product – Key Facts

Product:

Universal 880 Triple Ground

- Additional ground edge for improved cutting performance
- Universal use for multiple jobs & materials
- Proven handle design for comfortable, reliable cutting
- Available in 20" & 22"



PROVEN HANDLE DESIGN

Light and strong ultra sonic welded soft-grip handle for increased grip and enhanced comfort.

FINGER-REST

For maximum control.



0,85MM BLADE

High quality C75 steel is stable and ensures maximum power transfer.



WATER BASED LAQUER

Gives four times better rust protection than traditional laquer.



NEW

UNIVERSAL TRIPLE GROUND TOOTH

This unique new triple ground tooth design makes the new IRWIN-Jack 880 Triple Ground **25% faster*** than the double ground version.



HARDENED TEETH

Hard Point teeth (HP) stay sharp 6-8 times longer than non-hardened teeth.



UNIVERSAL USE

Tooth pitch designed to perform in multiple materials & jobs.



MULTI SET-PATTERN

Optimised set-pattern to help with smoothness of cut and more efficient saw dust removal.



MARKING ANGLES

90° & 45° angles integrated in the handle for ease of marking out.



NOW 25% FASTER!

*vs. IRWIN® 880 Universal double ground

Universal 880 Triple Ground					
Part #	Description	EAN	Shelf pack	List Price excl. VAT £	List Price incl. VAT £
10505212	Universal 880 Triple Ground, 20"/500mm HP 8T/9P	5706915052121	10	10.27	12.07
10505213	Universal 880 Triple Ground, 22"/550mm HP 8T/9P	5706915052138	10	10.56	12.41