



Adhesives

## MP100

### MULTI-PURPOSE SPRAY ADHESIVE

MP100 Multi Purpose Spray Adhesive is a fast drying, strong adhesive, ideal for bonding almost anything to most hard surfaces including wood and metal.

#### ADVANTAGES

- Original Formulation
- Fast Tack
- Ideal where instant contact and bonding is required
- Provides high-strength, permanent bonds
- Variable actuator for maximum control and economy
- Big value 500ml fill size

### PRODUCT CODES / FILL SIZES



31624 / 500ml

### APPLICATIONS

MP100 Multi Purpose Spray Adhesive will provide quick, strong bonds in many areas:

- Carpets & Flooring
- Chipboard and Concrete
- Insulation Materials
- Canvas and Leather
- Paper, Wood and Cork
- Metal, Plastics and Rubber

### DIRECTIONS

- Apply an even coating to both surfaces to be bonded from 9" – 12" (25 – 30cm)
- Wait until the adhesive is tack-dry and bond the surfaces together using firm pressure
- After user, to prevent blockages, invert the can and spray clear the nozzle

## TECHNICAL DATA (WITHOUT PROPELLANT)

Appearance	Thick, gelatinous film
Odour	Ethereal/Solvent
SG @ 25°C	1.16
Pressure @ 25°C	4 bar
Discharge rate	1.4g/sec
Polymer Type	Styrene butadiene rubber
Tack Time	Approximately 30 seconds
Bonding Time	Maximum adhesion in 12 - 24 hours
Temperature Range	Up to 50°C (dried film)
Solubility	Soluble in some solvents, insoluble in water
Recommended solvents	Amberklene FE10, ME20 or LO30
Flammability	Classified as extremely flammable under the EC Classification, Labelling and Packaging regulation (CLP) 1272/2008

## MATERIALS COMPATIBILITY

OK	-
CAUTION	May affect certain plastics. Always test a small, inconspicuous area before general use.
NOT OK	-

## STORAGE & SHELF LIFE

The product may be stored at normal ambient temperatures and has a shelf life of not less than 3 years with correct storage. Aerosols should always be stored below 50°C, away from direct heat and naked flame.

## HEALTH AND SAFETY

A separate Safety Data Sheet (SDS) according to EC Regulation 73/404/EEC and 648/2004/EC is available from Ambersil.com or via [info.uk@crcind.com](mailto:info.uk@crcind.com)

## MISREPRESENTATION ACT 1967

## TRADE DESCRIPTIONS ACT 1968

The information given in this publication is based on our experience and reports from customers. There are many factors outside our control and knowledge which affect the use and performance of our products and for which reason no warranty is given, express or implied. Users should make their own tests to determine the applicability of such information or the suitability of any products for their own particular purposes. Statements concerning the use of the products described herein are not to be construed as recommending the infringement of any patent and no liability for infringement arising out of any such use is to be assumed.

Version 3.1  
Created: July 2019  
Updated: October 2020

CRC Industries UK Ltd.  
Wyllys Road, Bridgwater  
Somerset, TA6 4DD  
United Kingdom

t +44 (0)1278 727200  
f +44 (0)1278 425644  
e [sales.uk@crcind.com](mailto:sales.uk@crcind.com)  
w [www.ambersil.com](http://www.ambersil.com)

Company Registered No. 04910479

VAT No. GB 821 5195 42

