

Araldite®

professional adhesives




Araldite® Repair 50g Bar

Araldite® Repair 50g Bar is a hard, long lasting solvent-free multi purpose repair putty which is waterproof and can be drilled, filled, painted or sanded.

Important

Bonds to most materials. Recommended for metal pipes, tanks, radiators, tools and equipment, guttering and stripped threads.

Make sure surfaces are clean and free from dust, corrosion, dirt and grease. For optimum bonding, slightly roughen surfaces with sandpaper and degrease metals with a suitable solvent. For a smooth repair surface, flatten with a damp cloth prior to the material hardening. After 5 –10 minutes the putty will harden and start to form a strong repair. After 72 hours, the putty can be drilled or sanded.



How to apply

Araldite® Repair is a strong putty which sets extremely hard. Fills gaps for uneven breaks. Sets in wet conditions. Water, oil, chemical and impact resistant. High temperature resistance (-40°C to 120°C). Withstands rough handling. Do not use to repair or bond items that will contact food or drink. Not recommended for bonding rear-view mirrors to car windscreens.

Storage

Should be stored in a dry place at room temperature.

New

Environmentally friendly product formulation plus eco-friendly packaging for easy recycling.

Copyright© 2011. Huntsman Advanced Materials (Switzerland) GmbH. All Rights Reserved.

Araldite® is a registered trademark of Huntsman Corporation or an affiliate thereof in one or more, but not all countries.

www.go-araldite.com