

Productname : POOL & SNOOKER CLOTH CLEANER Creationdate : 16.02.15 Version : 1.0
Ref.Nr.: UDS000010_3_20150216 (EN) Replaces: UK10063

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

POOL & SNOOKER CLOTH CLEANER
Aerosol

1.2. Relevant identified uses of the substance or mixture and uses advised against

Speciality

1.3. Details of the supplier of the safety data sheet

CRC Industries UK Ltd.
Ambersil House - Wylds Road
Castlefield Industrial Estate
TA6 4DD Bridgwater Somerset
United Kingdom
Tel.: +44 1278 727200
Fax.: +44 1278 425644
E-mail : hse.uk@crcind.com

1.4. Emergency telephone number

(+44)(0)1278 72 7200

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No 1272/2008

Physical:	Aerosols, category 1 Extremely flammable aerosol. Pressurised container: May burst if heated.
Health:	Eye irritation, category 2 Causes serious eye irritation. Specific target organ toxicity - single exposure, category 3 May cause drowsiness or dizziness.
Environment:	Not classified

Classification according to 67/548/EEC or 1999/45/EC:

EXTREMELY FLAMMABLE
Xi : IRRITANT





Productname : POOL & SNOOKER CLOTH CLEANER **Creationdate :** 16.02.15 Version : 1.0
Ref.Nr.: UDS000010_3_20150216 (EN) **Replaces:** UK10063

Health: R36: Irritating to eyes.
R67: Vapours may cause drowsiness and dizziness.
Physical: R12: Extremely flammable.
EXTREMELY FLAMMABLE
Environment: Not classified

2.2. Label elements

Labelling according to Regulation (EC) No 1272/2008

Product identifier: Contains:
propan-2-ol; isopropyl alcohol ;isopropanol

Hazard pictogram(s):  

Signal word: Danger

Hazard statement(s): H222 : Extremely flammable aerosol.
H229 : Pressurised container: May burst if heated.
H319 : Causes serious eye irritation.
H336 : May cause drowsiness or dizziness.

Precautionary statement(s): P102 : Keep out of reach of children.
P210 : Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
P211 : Do not spray on an open flame or other ignition source.
P251 : Do not pierce or burn, even after use.
P261 : Avoid breathing dust/fume/gas/mist/vapours/spray.
P271 : Use only outdoors or in a well-ventilated area.
P410/412 : Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F.
P501-2 : Dispose of contents/container to an authorised waste collection point.

2.3. Other hazards

None

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable.

3.2. Mixtures

Hazardous ingredient	CAS-nr.	EC-nr	w/w %	symbol	R-phrases*	Notes
propan-2-ol; isopropyl alcohol ;isopropanol	67-63-0	200-661-7	30-60	F,Xi	11-36-67	B
Hydrocarbons,C3-4-rich, petroleum distillate Petroleumgas (1,3-butadiene < 0.1%)	68512-91-4	270-990-9	5-10	F+	12	K,G

Productname : POOL & SNOOKER CLOTH CLEANER **Creationdate :** 16.02.15 Version : 1.0
Ref.Nr.: UDS000010_3_20150216 (EN) **Replaces:** UK10063

ammonia %	1336-21-6	215-647-6	0-1	C,N	34-50	
----------------	-----------	-----------	-----	-----	-------	--

Explanation notes

B : substance with national established workplace exposure limit

G : exempted from the obligation to register in accordance with art.2(7)(a)of REACH Regulation No 1907/2006

K : not classified as carcinogen, less than 0.1% w/w 1,3-butadiene (Einecs-nr. 203-450-8)

Hazardous ingredient	Registration number	CAS-nr.	EC-nr	w/w %	Hazard Class and Category	Hazard statement	Notes
propan-2-ol; isopropyl alcohol ;isopropanol	01-2119457558-25	67-63-0	200-661-7	30-60	Flam. Liq. 2, Eye Irrit. 2, STOT SE 3	H225,H319,H336	B
Hydrocarbons,C3-4-rich, petroleum distillate Petroleumgas (1,3-butadiene < 0.1%)	-	68512-91-4	270-990-9	5-10	Press. Gas, Flam. Gas 1	H280,H220	K,G
ammonia %		1336-21-6	215-647-6	0-1	Skin Corr. 1B, Aquatic Acute 1	H314,H400	

Explanation notes

B : substance with national established workplace exposure limit

G : exempted from the obligation to register in accordance with art.2(7)(a)of REACH Regulation No 1907/2006

K : not classified as carcinogen, less than 0.1% w/w 1,3-butadiene (Einecs-nr. 203-450-8)

(* Explanation phrases : see chapter 16)

SECTION 4: First aid measures**4.1. Description of first aid measures**

Contact with eyes :	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention.
Contact with skin :	Take off contaminated clothing and wash before reuse. IF ON SKIN: Wash with plenty of soap and water. If skin irritation occurs: Get medical advice/attention.
Inhalation :	IF INHALED: Remove person to fresh air and keep comfortable for breathing. Call a POISON CENTER or doctor/physician if you feel unwell.
Ingestion :	If swallowed accidentally, do not induce vomiting and seek medical advice.

4.2. Most important symptoms and effects, both acute and delayed

Inhalation :	Excessive inhalation of solvent vapours may give rise to nausea, headaches and dizziness
Ingestion :	May cause gastrointestinal disturbances Symptoms : sore throat, abdominal pain, nausea, vomiting
Skin contact :	May cause irritation. Symptoms : redness and pain
Eye contact :	Irritating to eyes Symptoms : redness and pain

4.3. Indication of any immediate medical attention and special treatment needed

General Advice :	If you feel unwell, seek medical advice (show the label where possible) If symptoms persist always call a doctor
-------------------------	---

Productname : POOL & SNOOKER CLOTH CLEANER Creationdate : 16.02.15 Version : 1.0
Ref.Nr.: UDS000010_3_20150216 (EN) Replaces: UK10063

SECTION 5: Firefighting measures

5.1. Extinguishing media

foam, carbon dioxide or dry agent

5.2. Special hazards arising from the substance or mixture

Aerosols may explode if heated above 50°C
Forms hazardous decomposition products
CO,CO2

5.3. Advice for firefighters

Keep container(s) exposed to fire cool, by spraying with water
In case of fire, do not breathe fumes

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Shut off all ignition sources
Ensure adequate ventilation
Wear suitable protective clothing and gloves.

6.2. Environmental precautions

Do not allow to enter public sewers and watercourses
If polluted water reaches drainage systems or water courses, immediately inform appropriate authorities

6.3. Methods and material for containment and cleaning up

Absorb spillage in suitable inert material
Place in appropriate container

6.4. Reference to other sections

For further information see section 8

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Keep away from heat and sources of ignition
Take precautionary measures against static discharges
Equipment should be earthed
Use explosion-proof electrical/ventilating/lighting/.../equipment.
Use only non-sparking tools.

Productname : POOL & SNOOKER CLOTH CLEANER **Creationdate :** 16.02.15 Version : 1.0
Ref.Nr.: UDS000010_3_20150216 (EN) **Replaces:** UK10063

Do not breathe aerosols or vapours.
 Ensure adequate ventilation
 Avoid contact with skin and eyes.
 Wash thoroughly after use
 Wear protective gloves/protective clothing/eye protection/face protection.
 Eyewash bottles should be available

7.2. Conditions for safe storage, including any incompatibilities

Pressurized container : protect from sunlight and do not expose to temperatures exceeding 50°C.
 Keep out of reach of children.

7.3. Specific end use(s)

Speciality

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Exposure limits :

Hazardous ingredient	CAS-nr.	method	
EU established exposure limits:			
propan-2-ol; isopropyl alcohol ;isopropanol	67-63-0	TWA	400 ppm
		STEL	500 ppm

8.2. Exposure controls

Control procedures : Ensure adequate ventilation
 Keep away from heat and sources of ignition
 Take precautionary measures against static discharges

Personal protection : Take precautions to avoid contact with skin and eyes when handling the product.
 Ensure adequate ventilation

inhalation : In case of insufficient ventilation, wear suitable respiratory equipment.

hands and skin : Wear suitable protective gloves against chemicals

Recommended gloves: Nitrile

eyes : Wear safety goggles.

Environmental protection: Avoid release to the environment.
 Collect spillage.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

(for aerosols data for the product without propellant)

Apperance : physical state : Propane/butane propelled liquid.

Productname : POOL & SNOOKER CLOTH CLEANER **Creationdate :** 16.02.15 Version : 1.0
Ref.Nr.: UDS000010_3_20150216 (EN) **Replaces:** UK10063

colour : Colorless.
odour : Characteristic odor.
pH : Not available.
Boiling point/range : 82 °C
Flash point : 12 °C
Evaporation rate : Not available.
Explosion limits : upper limit : 12 %
lower limit : 1.8 %
Vapour pressure : Not available.
Relative density : 0.935 g/cm³ (@ 20°C).
Solubility in water : Soluble in water
Auto-ignition : 460 °C
Viscosity : Not available.

9.2. Other information

SECTION 10: Stability and reactivity

10.1. Reactivity

No hazardous reactions known if used for its intended purpose

10.2. Chemical stability

Stable

10.3. Possibility of hazardous reactions

No hazardous reactions known if used for its intended purpose

10.4. Conditions to avoid

Avoid overheating

10.5. Incompatible materials

Strong oxidising agent

10.6. Hazardous decomposition products

CO,CO₂

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Information on likely routes of exposure:

Productname : POOL & SNOOKER CLOTH CLEANER **Creationdate :** 16.02.15 Version : 1.0
Ref.Nr.: UDS000010_3_20150216 (EN) **Replaces:** UK10063

Inhalation : Inhalation of solvent vapours may give rise to nausea, headaches and dizziness
Ingestion : May cause gastrointestinal disturbances
Skin contact : May cause irritation.
Eye contact : Irritating to eyes

Toxicological data :

Hazardous ingredient	CAS-nr.	method	
propan-2-ol; isopropyl alcohol ;isopropanol	67-63-0	LD50 oral rat	> 5000 mg/kg
		LC50 inhal.rat	> 20 mg/l
		LD50 derm.rabbit	> 5000 mg/kg

SECTION 12: Ecological information**12.1. Toxicity**

Not classified

Ecotoxicological data:

Hazardous ingredient	CAS-nr.	method	
propan-2-ol; isopropyl alcohol ;isopropanol	67-63-0	IC50 algae	> 1000 mg/l
		LC50 fish	> 1000 mg/l
		EC50 daphnia	> 1000 mg/l

12.2. Persistence and degradability

No information available

12.3. Bioaccumulative potential

No information available

12.4. Mobility in soil

Soluble in water

12.5. Results of PBT and vPvB assessment

No information available

12.6. Other adverse effects

No information available

Productname : POOL & SNOOKER CLOTH CLEANER Creationdate : 16.02.15 Version : 1.0
Ref.Nr.: UDS000010_3_20150216 (EN) Replaces: UK10063

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Product : This material and its container must be disposed of in a safe way.
Do not discharge into drains or the environment, dispose to an authorised waste collection point.

National regulations : Disposal should be in accordance with local, state or national legislation

SECTION 14: Transport information

14.1. UN number

UN-number : 1950

14.2. UN proper shipping name

Proper shipping name: AEROSOLS

14.3. Transport hazard class(es)

Class: 2.1
ADR/RID - Classification code: 5F

14.4. Packing group

Packing group: Not applicable.

14.5. Environmental hazards

ADR/RID - Environmentally hazardous: No
IMDG - Marine pollutant: No
IATA/ICAO - Environmentally hazardous: No

14.6. Special precautions for user

ADR/RID - Tunnelcode: (D)
IMDG - Ems: F-D, S-U
IATA/ICAO - PAX: 203
IATA/ICAO - CAO: 203

14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code

Not applicable.

Productname : POOL & SNOOKER CLOTH CLEANER Creationdate : 16.02.15 Version : 1.0
Ref.Nr.: UDS000010_3_20150216 (EN) Replaces: UK10063

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

The Safety Data Sheet is compiled according to the current European requirements.
Dir. 2013/10/EU, 2008/47/EC amendment of the aerosol dispenser directive 75/324/EEC.
EU-directive 99/45/EC
Regulation (EC) No 1272/2008 (CLP)
Regulation (EC) No 1907/2006 (REACH)

15.2. Chemical safety assessment

No information available

SECTION 16: Other information

*Explanation risk-phrases: R11: Highly flammable.
R12: Extremely flammable.
R34: Causes burns.
R36: Irritating to eyes.
R50: Very toxic to aquatic organisms.
R67: Vapours may cause drowsiness and dizziness.

*Explanation hazard statements: H220 : Extremely flammable gas.
H225 : Highly flammable liquid and vapour.
H280 : Contains gas under pressure; may explode if heated.
H314 : Causes severe skin burns and eye damage.
H319 : Causes serious eye irritation.
H336 : May cause drowsiness or dizziness.
H400 : Very toxic to aquatic life.

This product should be stored, handled and used in accordance with good industrial hygiene practices and in conformity with any legal regulation.

The information contained herewith is based on the present state of our knowledge and is intended to describe our products from the point of view of safety requirements. It does not guarantee any specific properties. Apart from any fair dealing for purposes of study, research and review of health, safety and environmental risks, no part of these documents may be reproduced by any process without written permission from CRC.