

3M Science.
Applied to Life.™



Three duct tapes that can do it all

3M™ Duct Tapes DT Series



Be equipped for the day

Tackle your everyday tasks with 3M™ Duct Tapes DT Series in three strengths. They resist curling, have a consistent unwind and tear off the roll cleanly for the ultimate in ease of handling and application.

Enlarged photo to show unique texture of 3M™ Super Duty Duct Tape DT17.



The rolls you always want to keep on hand

3M™ Duct Tapes DT Series offer hand tearability, high tensile strength and conformability.



**3M™ All Purpose
Duct Tape DT8**

Conformable with instant bond

Unique design offers high instant adhesion coupled with maximum conformability.



- Ideal for contoured surfaces and quick labeling
- Good tensile strength for light-duty bundling
- Use for quick repairs, splicing, temporary holding and fast attachments



**3M™ Heavy Duty
Duct Tape DT11**

Versatility with holding power

Good holding power with a broad attribute performance make this the go-to choice for demanding jobs.



- Sticks immediately and stays on irregular, hard-to-bond surfaces without lifting — even on most plastics
- Water-resistant, polyethylene backing resists wear and light abrasion — good for securing temporary floor coverings
- Moisture-resistant seal in many containment situations, such as pipe sealing and attaching heavy poly draping
- Low-tack roll edges so rolls stay cleaner



**3M™ Super Duty
Duct Tape DT17**

Super thick for super tough jobs

Ultra-thick, water-resistant backing resists wear and abrasion while still tearing easily by hand.



- Aggressive rubber adhesive grips instantly to a variety of surfaces including metal, glass, plastic and sealed concrete
- Excellent for repairing, seaming, extra-strength bundling and helps in protecting metal parts and surfaces against sandblast overspray
- Superior strength for the most demanding applications
- Low-tack roll edges so rolls stay cleaner

Duct tape simplified

Three tapes in three strengths to tackle the bulk of your everyday duct taping tasks.

3M™ DT Series	Backing material	Adhesive type	Thickness (mm)	Tensile strength N/cm	Elongation at break %	Adhesion to steel N/cm	Instant adhesion	Roll size	Color
Based on ASTM Test Method:			D-3652*	D-3759	D-3759	D-3330			
3M™ All Purpose Duct Tape DT8	Polyethylene film over cloth scrim	Synthetic/natural rubber blend	0.20	40.7	20%	7.5	✓	48 mm x 54.8 m	Silver, Black
								48 mm x 22.9 m	Silver, Black
3M™ Heavy Duty Duct Tape DT11	Polyethylene film over cloth scrim	Synthetic/natural rubber blend	0.27	49	20%	8.4	✓	48 mm x 54.8 m	Silver, Black
3M™ Super Duty Duct Tape DT17	Polyethylene film over cloth scrim	Synthetic/natural rubber blend	0.42	65.7	18%	9.2	✓	48 mm x 32 m	Black

*ASTM D-3652 tested at 2.7 psi (18kPa).

Product Selection and Use: Many factors beyond 3M's control and uniquely within users' knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customers' application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.



3M Closure and Masking Systems Division

3M United Kingdom PLC
3M Centre, Cain Road
Bracknell, Berkshire RG12 8HT
Phone 0870 6080050
www.3M.co.uk

3M Ireland Limited
The Iveagh Building
Carrickmines 18
Phone 353-1-280355
www.3Mireland.ie

3M is a trademark of 3M. © 3M 2021.
All rights reserved. Please recycle.
(04/2021)



- Patching
- Bundling
- Reinforcing
- Taping/splicing insulation
- Capping pipe
- Securing conduit ends
- Marking
- Labeling
- Performing temporary repairs
- Hanging polyethylene drapes
- Protecting against sandblast overspray