



Double sided adhesive tape GPT-020F

Product Data Sheet

December 2019

Supersedes: October 2019

Product Description

Double sided adhesive tape with polyester carrier
Modified acrylic adhesive Film Liner

Key Features

- High adhesion to a variety of high and low surface energy substrate
- High initial tack
- All-purpose tape
- High shear and temperature resistance
- Easy handling and converting due to polyester carrier
- Film Liner for clean handling and automatic unwinding activities

Application ideas

- Self-adhesive mounting of furniture trim, sealing profiles and cable ducts.
- Bonding and mounting of sales displays and billboards.
- Fixing of decorative trims and emblems.

Construction

Adhesive	Modified Acrylic
Adhesive side open face ¹	0,095 mm
Carrier	PET 0,012 mm, transparent
Adhesive back side ²	0,095 mm
Total thickness without liner	0,202 mm
Liner	Polypropylene film liner, white (0,100 ± 0,010 mm)

¹The open face side is visible, when unwinding the roll.

²The back side is visible after removal of the liner.

Calipers are average values.

Calculation of the adhesive caliper based on an average density of 1.012 g/ cm³.

Performance Characteristics

Adhesion to Stainless Steel acc. to Finat FTM1 (after 72 h at RT, angle: 180°, Haul-off speed: 300 mm/min., (0,05 mm PET-Film)	11,30 N/cm
Adhesion to ABS acc. to Finat FTM1 (after 72 h at RT, angle: 180°, Haul-off speed: 300 mm/min., (0,05 mm PET-Film)	10,86 N/cm
Adhesion to Polycarbonate acc. to Finat FTM1 (after 72 h at RT, angle: 180°, Haul-off speed: 300 mm/min., (0,05 mm PET-Film)	12,32 N/cm
Adhesion to Polypropylene acc. to Finat FTM1 (after 72 h at RT, angle: 180°, Haul-off speed: 300 mm/min., (0,05 mm PET-Film)	12,26 N/cm
Adhesion to Glass acc. to Finat FTM1 (after 72 h at RT, angle: 180°, Haul-off speed: 300 mm/min., (0,05 mm PET-Film)	11,79 N/cm
Static shear resistance to stainless steel acc. to Finat FTM8, 1 kg/ 1"x1", at RT	> 10.000 min
Static shear resistance to stainless steel acc. to Finat FTM8; 500 g /0.5"x1" at 90 °C	>10.000 min
Temperature Performance (SAFT, PSTC 17, 40 °C to 205 °C, 0.5 °C / min), 500 g / 1"x1"	> 190 °C
Temperature Performance (SAFT, PSTC 17, 40 °C to 205 °C, 0.5 °C / min), 1000 g / 1"x1"	> 160 °C

Storage & Shelf Life

Store at 16 °C–25 °C and 40-65 % relative humidity in its original box.
The product can be stored up to 18 months after date of manufacturing.

Note: The shelf life may be shortened if the original packaging is not properly sealed or stored in an environment with high temperatures or humidity

Precautionary Information

For information please contact your local 3M Office.
www.3M.com

For Additional Information

To request additional product information or to arrange for sales assistance, call.....
Address correspondence to: 3M

Important Notice

All statements, technical information and recommendations contained in this document are based upon tests or experience that 3M believes are reliable. However, many factors beyond 3M's control can affect the use and performance of a 3M product in a particular application, including the conditions under which the product is used and the time and environmental conditions in which the product is expected to perform. Since these factors are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for the user's method or application. All questions of liability relating to this product are governed by the terms of the sale subject, where applicable, to the prevailing law

Values presented have been determined by standard test methods and are average values not to be used for specification purposes. Our recommendations on the use of our products are based on tests believed to be reliable but we would ask that you conduct your own tests to determine their suitability for your applications. This is because 3M cannot accept any responsibility or liability direct or consequential for loss or damage caused as a result of our recommendations

3M is a trademark the 3M Company.

**3M Industrial Adhesive and Tapes Division**

3M United Kingdom plc
3M Centre
Cain Road, Bracknell
Berkshire RG12 8HT
0870 60 800 50

3M Ireland Ltd
The Iveagh Building
The Park, Carrickmines
Dublin 18
Tel: 1 800 320 500