



ESD Scissors

Features:

- Colour: Black
- Test Method: Two Point Resistance as per ANSI/ESD STM 11.13-2C
- Surface Resistance 105-108 Ω
- Friction Voltage: less than 100V
- Permanently Antistatic

Application: To be used in EPA and clean room environments.

Product tested at both 12% and 50% RH at 23°C



Product Code	Description	Length (mm)	Additional Notes
157-0007	ESD Scissors (black)	178mm	Each

Important Notice: This data sheet and its contents (the "Information") belong to Antistat or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but Antistat assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where Antistat was aware of the possibility of such loss or damage arising) is excluded. © Antistat.



WWW.ANTISTAT.CO.UK