



NOTE: It is our policy to continually improve products and as such we reserve the right to alter data, specifications and component parts without prior notice.

IMPORTANT: No liability is accepted for incorrect use of product.

WARRANTY: Guarantee is 12 months from purchase date, proof of which will be required for any claim.



Parts Information:
Pillar Drill Floor 12-Speed
Model No: GDM92B & GDM140F

Item	Part No.	Description
1	GDM92B/01	BASE (GDM92B only)
1	GDM140F/01	BASE (GDM140F only)
2	GDM92B/02	BOLT M10x25
3	GDM92B/03	COLUMN (GDM92B only)
3	GDM140F/03	COLUMN (GDM140F only)
4	GDM92B/04	RACK RING
5	GDM92B/05	HEADLESS SET SCREW
6	GDM92B/06	RACK (GDM92B only)
6	GDM140F/06	RACK (GDM140F only)
7	GDM92B/07	TABLE ARM BRACKET
7A	GDM92B/07A	TABLE ARM
8	SN8.S	STEEL NUT M8 ZINC DIN934 (SINGLE)
9	GDM92B/09	WORM GEAR
10	GDM92B/10	GEAR
11	GDM92B/11	SHAFT
12	GDM92B/12	HANDLE
13	GDM92B/13	SET BOLT
14	GDM92B/14	PLUG
15	GDM92B/15	CLAMP BOLT
15A	GDM92B/15A	TABLE BOLT
16	GDM92B/16	TABLE
17	MSP510.S	MACHINE SCREW PAN HEAD PHILLIPS M5x10mm
18	FWM5.S	FLAT WASHER M5 SINGLE
19	SCB1230.SB	SOCKET CAP BOLT BLACK M12X30
20	GDM92B/20	CHUCK B16 3-16mm
21	GDM92B/21	ARBOR
22	GDM92B/22	SPINDLE
23	B/6204-2RS	BEARING 6204-2RS
24	GDM92B/24	SPINDLE SLEEVE
25	B/6201ZZ	BEARING 6201ZZ
26	GDM92B/26	RETAINING RING
27	GDM92B/27	RUBBER WASHER M40
28	GDM92B/28	FEED SHAFT
--	GDM92B/28A	FEED PART ASSY (NOT SHOWN)
29	GDM92B/29	CLAMP BOLT
30	GDM92B/30	SCALE RING
31	GDM92B/31	HANDLE BODY
32	GDM92B/32	HANDLE
33	GDM92B/33	KNOB
34	GDM92B/34	HEADLESS SET SCREW
35	SN8.S	STEEL NUT M8 ZINC DIN934 (SINGLE)
36	GDM92B/36	BODY
37	GDM92B/37	HEX.KEY
38	GDM92B/38	HEX.KEY
39	GSM812.S	GRUB SCREW M8x12 (SINGLE)
40	GDM92B/40	SLIDE BAR BOLT
41	GDM92B/41	SCREW

Item	Part No.	Description
42	GDM92B/42	SLIDE BAR
43	GDM92B/43	INSTRUCTION MANUAL
44	GDM92B/44	CHUCK KEY
45	GDM92B/45	SPRING
46	GDM92B/46	SPRING SEAT
47	GDM92B/47	M12 X 1.5 FINE PITCH HALF NUT
48	GDM92B/48	PLASTIC JAM NUT
49	GDM92B/49	SCREW 6 X 1/2" AB PAN SELF TAP SUPADRIVE
50	GDM92B/50	SWITCH (FRONT MOUNT WITH EMERGENCY STOP)
--	GDM92B/50A	SWITCH HOUSING (NOT SHOWN)
51	GDM92B/51	WIRE CLAMP
52	MSP410.S	MACHINE SCREW PAN HEAD PHILLIPS M4x10mm
53	GDM92B/53	MOTOR BASE
54	GDM92B/54	MOTOR (370W MAX NO LOAD 550W MAX LOAD)
--	WPC235.08	CAPACITOR (8uf)50/60HZ 65X30 (NOT SHOWN)
--	GDM92B/54-1	FAN COVER (NOT SHOWN)
--	GDM92B/54-2	CAPACITOR COVER (NOT SHOWN)
55	SS830.S	HEX HEAD SET SCREW M8x30mm SINGLE
56	GDM92B/56	WASHER
57	SN8.S	STEEL NUT M8 ZINC DIN934 (SINGLE)
58	GDM92B/58	V-BELT K-456
59	GDM92B/59	CENTRE PULLEY
60	GDM92B/60	HEADLESS SET SCREW
61	DPG99	DRILL PRESS GUARD 60mm
62	GDM92B/62	RETAINING RING
63	B/6203ZZ	BEARING 6203ZZ
64	GDM92B/64	COLLAR
65	GDM92B/65	DRIVE SLEEVE
66	GDM92B/66	SPINDLE PULLEY
67	GDM92B/67	PULLEY HALF NUT
68	MSP612.S	MACHINE SCREW PAN HEAD PHILLIPS M6x12mm
69	FWM6.S	FLAT WASHER M6 SINGLE
70	GDM92B/70	PULLEY COVER
71	GDM92B/71	V-BELT K550 (ID-515)
72	GDM92B/72	MOTOR PULLEY
73	GDM92B/73	CENTRE SHAFT
74	B/6202ZZ	BEARING 6202ZZ
75	GDM92B/75	NUT
76	GDM92B/76	WASHERS PLAIN AND SPRING M12
77	MSP514.S	MACHINE SCREW PAN HEAD PHILLIPS M5x14mm
78	GDM92B/50A	SWITCH HOUSING
79	GDM92B/79	WEDGE
80	GDM92B/80	PIN
81	GDM92B.81	MICRO SWITCH
82	GDM92B.82	MICRO SWITCH HOLDER
83	GDM92B.83	PHILLIPS BOLT M6x12
--	DPG99	DRILL PRESS GUARD 60mm (NOT SHOWN)

NOTE: It is our policy to continually improve products and as such we reserve the right to alter data, specifications and component parts without prior notice.

IMPORTANT: No liability is accepted for incorrect use of product.

WARRANTY: Guarantee is 12 months from purchase date, proof of which will be required for any claim.

Sealey Group, Kempson Way, Suffolk Business Park, Bury St Edmunds, Suffolk. IP32 7AR



01284 757500



01284 703534



sales@sealey.co.uk



www.sealey.co.uk