


Parts Information:

Metal Cutting Bandsaw 3-Speed 150mm 230V

Model No: SM5.V3



NOTE: It is our policy to continually improve products and as such we reserve the right to alter data, specifications and component parts without prior notice. IMPORTANT: No liability is accepted for incorrect use of product.

WARRANTY: Guarantee is 12 months from purchase date, proof of which will be required for any claim.

Sealey Group, Kempson Way, Suffolk Business Park, Bury St Edmunds, Suffolk. IP32 7AR



01284 757500



01284 703534









Parts Information:

Metal Cutting Bandsaw 3-Speed 150mm

Model No: SM5.V3

Item	Part No.	Description
1	MSP612.S	MACHINE SCREW PAN HEAD PHILLIPS M6x12mm
2	SM5.V3/02	HEXAGON NUT
3	FWM6.S	FLAT WASHER M6 SINGLE
4	SM5.V3/04	FLOOR STAND (RIGHT)(SO)
5	SM5.V3/05	WHEEL,FIXED (106x10x16)
6	SM5.V3/06	COTTER PIN
11	SM5.V3/11	HEXAGON HEAD SCREW
12	SN8.S	STEEL NUT M8 ZINC DIN934 (SINGLE)
13	SM5.V3/13	FLOOR STAND (LEFT) (SO)
14	SM5.V3/14	FLOOR STAND HANDLE (OPTIONAL)(SO)
15	SM5.V3/15	ADJUSTING ROD (SO)
16	SM5.V3/16	ELECTRIC CORD (SO)
17	SM5.V3/17	PIVOTING CORD
18	SM5.V3/18	SUPPORT PLATE
19	SM5.V3/19	STOCK STOP
20	SM5.V3/20	HEXAGON SOCKET HEADLESS SCREW
21	SM5.V3/21	STOCK STOP ROD
22	SM5.V3/22	WIRE RELIEF RETAINER
23	SM14C.V5-10	SWITCH 250VAC-6A
23A	SM5.V3-23A	HOUSING FOR SWITCH
26	SM5.V3/26	SWITCH PANEL
27	SM5.V3/27	ADJUSTING ROD SUPPORT
28	SM5.V3/28	HAND WHEEL (SO)
30	SM5.V3/30	CIRCLIP
32	SM5.V3/32	LEAD SCREW
33	SM5.V3/33	VICE NUT (SO)
34	SM5.V3/34	MOVABLE VICE PLATE
35	SM5.V3/35	REPAIR WASHER M10
36	SS1030.S	HEX HEAD SET SCREW M10x30mm SINGLE
37	SM5.V3/37	BED(SO)
39	SM5.V3/39	SCALE
43	SM5.V3/43	RUBBER RING (SO)
44	SM5.V3/44	ELECTRIC CORD
45	SM5.V3/45	NUT PLATE
46	SM5.V3/46	SPRING ADJUSTING SCREW
47	SM5.V3/47	SPRING
48	MSP48.S	MACHINE SCREW PAN HEAD PHILLIPS M4x8mm
49	SM5.V3/49	VICE PLATE

Item	Part No.	Description
50	SS1030.S	HEX HEAD SET SCREW M10x30mm SINGLE
51	SM5.V3/51	WASHER M10x25
52	SS830.S	HEX HEAD SET SCREW M8x30mm SINGLE
53	SM5.V3/53	HEXAGON HEAD SCREW (SO)
54	SM5.V3/54	PIVOTING ROD BRACKET
55	SM5.V3/55	VERTICAL CUTTING PLATE
56	SM5.V3/56	STAND, VERTICAL CUTTING PLATE
57	SM5.V3/57	ADJUSTABLE BRACKET (LEFT)(SO)
58	SM5.V3/58	THUMB SCREW
59	SM5.V3/59	BLADE BACK SAFETY PANEL
60	SM5.V3/60	THRUST WASHER
61	B/629ZZ	BEARING 629ZZ
62	SM5.V3/62	GUIDE PIVOT
63	SM5.V3/63	BEARING SHAFT PIN
64	SM5.V3/64	BLADE ADJUSTABLE SEAT
65	SM5.V3/65	ADJUSTABLE BRACKET (RIGHT)
66	SS1030.S	HEX HEAD SET SCREW M10x30mm SINGLE
67	SWM10.S	SPRING WASHER M10 ZINC (SINGLE)
68	MSC616.S	CSK PHILLIPS MACHINE SCREW M6x16 (SINGLE
69	SM5.V3/69	BLADE GUARD
70	SN10.S	STEEL NUT M10 ZINC DIN934(SINGLE)
71	SM5.V3/71	BLADE WHEEL (FRONT)
71A	SM5.V3-71A	BUSH
72	SM5.V3/72	BLADE WHEEL BEARING COVER
73	SM5.V3/73	KEY
75	SS616.S	HEX HEAD SET SCREW M6x16mm SINGLE
76	SM5.V3/76	SWITCH CUT OFF TIP
77	SM5.V3/77	BLADE WHEEL (REAR)
79	SM5.V3/79	BLADE TENSION ADJUSTABLE KNOB
80	SM5.V3/80	SPRING
81	SM5.V3/81	BODY FRAME
83	SS830.S	HEX HEAD SET SCREW M8x30mm SINGLE
84	SM5.V3/84	MOTOR MOUNT PLATE
85	SM5.V3/85	MOTOR
86	SM5.V3/86	MOTOR PULLEY
87	B/6202Z	BEARING 6202Z
88	SM5.V3/88	BEARING BUSHING
89	SM5.V3/89	OIL SEAL
90	SM5.V3/90	TRANSMISSION WHEEL SHAFT

NOTE: It is our policy to continually improve products and as such we reserve the right to alter data, specifications and component parts without prior notice. IMPORTANT: No liability is accepted for incorrect use of product.

WARRANTY: Guarantee is 12 months from purchase date, proof of which will be required for any claim.

Sealey Group, Kempson Way, Suffolk Business Park, Bury St Edmunds, Suffolk. IP32 7AR



01284 757500



01284 703534



sales@sealey.co.uk





Parts Information:

Metal Cutting Bandsaw 3-Speed 150mm

Model No: SM5.V3

Item	Part No.	Description
91	SM5.V3/91	TRANSMISSION GEAR
92	SM5.V3/92	GEAR BOX GASKET
93	SM5.V3/93	GEAR BOX COVER
94	SM5.V3/94	WORM GEAR
96	SM5.V3/96	BEARING BUSHING(SO)
98	SM5.V3/98	PLUM SCREW
99	FWM6.S	FLAT WASHER M6 SINGLE
100	MSP48.S	MACHINE SCREW PAN HEAD PHILLIPS M4x8mm
101	SM5.V3/101	WORM GEAR PULLEY
103	SM5.V3/103	BLADE TENSION SLIDING PLATE
104	SM5.V3/104	HEXAGON SOCKET HEADLESS SCREW(SO)
105	SM5.V3/105	SPRING PIN
106	SM5.V3/106	SLIDING PLATE DRAW BLOCK
107	SM5.V3/107	BLADE WHEEL SHAFT
108	SM5.V3/108	SHAFT BLOCK
109	SM5.V3/109	BLADE TENSION SLIDING GUIDES
110	SM5.V3/110	MOTOR PULLEY COVER
112	V/M20	V-BELT (ID-515) M20
113	SM5/113	BLADE
114	SWM10.S	SPRING WASHER M10 ZINC (SINGLE)
117	FWM6.S	FLAT WASHER M6 SINGLE
118	SM5.V3/118	THRUST WASHER
120	SM5.V3/120	COLLAR
122	SN8.S	STEEL NUT M8 ZINC DIN934 (SINGLE)
126	SM5.V3/126	BUSHING
131	SM5.V3/131	SWITCH PROTECTION BRACKET

Item	Part No.	Description
132	SM5.V3/132	BLADE SAFETY GUARD
134	SM5.V3/134	SCREW
140	SN4.S	STEEL NUT M4 ZINC DIN934 (SINGLE)
156	SM5.V3/156	ROUND HEAD CROSS SOCKET SCREW
157	SM5.V3/157	STAR WASHER
169	SM5.V3/169	CROSS SOCKET SCREW
170	SM5.V3/170	TOOL PLATE
171	SM5.V3/171	HEXAGON HEAD SCREW
172	SM5.V3/172	HEXAGON NUT
173	FWM6.S	FLAT WASHER M6 SINGLE
174	SM5.V3/174	WHEEL STAND
175	SM5.V3/175	COTTER PIN
176	SM5.V3/176	AXLE(SO)
177	PDM.MS	MICRO SWITCH FOR PDM DRILLS
178	SM5.V3-178	COVER FOR MICRO SWITCH
179	SM5.V3-179	TERMINAL BOX
180	SM5.V3-180	TERMINAL
	SM5/113	BANDSAW BLADE 1638 x 13 x 0.63mm 14tpi (NOT SHOWN)
	SM5/113/6	BANDSAW BLADE 1638 x 13 x 0.63mm 6tpi (NOT SHOWN)
	SM5/113/10	BANDSAW BLADE 1638 x 13 x 0.63mm 10tpi (NOT SHOWN)
	SM5/113/24	BANDSAW BLADE 1638 x 13 x 0.63mm 24tpi (NOT SHOWN)
180	SM5.V3/181	ADJUSTABLE BLADE ASSY
	SM5.V3/182	ANGLE BRACKET (NOT SHOWN)
	SM5.V3-23A	HOUSING FOR SWITCH (NOT SHOWN)

NOTE: It is our policy to continually improve products and as such we reserve the right to alter data, specifications and component parts without prior notice. IMPORTANT: No liability is accepted for incorrect use of product.

WARRANTY: Guarantee is 12 months from purchase date, proof of which will be required for any claim.



01284 757500



01284 703534



sales@sealey.co.uk

