


## Parts Information: Wood Lathe 1000mm Model No: SM1308



Item	Part No.	Description
2	SM1308.02	CORD CLAMP
3	MSP510.S	MACHINE SCREW PAN HEAD PHILLIPS
		M5x10mm
4	SM1308.04	WASHER
5	SM1308.05	BELT PULLEY
6	GSM610.S	GRUB SCREW M6x10 (SINGLE)
7	SS816.S	HEX HEAD SET SCREW M8x16mm SINGLE
8	FWM8.S	FLAT WASHER M8 SINGLE
9	SM1308.09	SCREW
10	FWM5.S	FLAT WASHER M5 SINGLE
11	SM1308.11	PROTECTING GUARD
12	SM1308.12	V-BELT (9MM ID-480)
13	SM1308.13	BELT PULLEY
14	SM1308.14	MOTOR SCREW
15	FWM8.S	FLAT WASHER M8 SINGLE
16	SM1308.16	LOCKING SCREW
19	B/6203-2RS	BEARING 6203-2RS
20	SM1308.20	BEARING BLOCK
22	SM1308.22	SPANNER
23	SM1308.23	BEARING BLOCK
24	B/6204-2RS	BEARING 6204-2RS
25	FWM8.S	FLAT WASHER M8 SINGLE
26	SS816.S	HEX HEAD SET SCREW M8x16mm SINGLE
27	SM1308.27	AXIS
28	SM1308.28	LATHE TIP

	Durth	Description
Item	Part No.	Description
29	SM1308.29	FACE PLATE
30	SM46C/16	SWITCH - KJD12
33	SM1308.33	JIP
34	SS1880.S	HEX HEAD SET SCREW M18x80mm SINGLE
35	SM1308.35	CARRIAGE
37	SM1308.37	TIP
38	B/6201-2RS	BEARING 6201-2RS
39	SM1308.39	TAILSTOCK
40	SN18.S	STEEL NUT M18 ZINC DIN934(SINGLE)
41	SM1308.41	SCREW AXIS
42	GSM610.S	GRUB SCREW M6x10 (SINGLE)
43	SM1308.43	HANDWHEEL
53	SM1308.53	GUIDE PLATE
54	SN18.S	STEEL NUT M18 ZINC DIN934(SINGLE)
59	SM1308.59	KNOB
60	SM1308.60	GUIDE PLATE
61	SN18.S	STEEL NUT M18 ZINC DIN934(SINGLE)
65	SM1308.65	SCREW FOR SWITCH
68	SM1308.68	PLATE
72	SM1308.72	MOTOR
75	SM1308.75	CAP
76	SM1308.76	CAP
	SM1308.77	TRANSPARENT PLATE (NOT SHOWN)
	CPG12V.V2-A11	MICRO SWITCH (NOT SHOWN)

NOTE: It is our policy to continually improve products and as such we reserve the right to alter data, specifications and component parts without prior notice. IMPORTANT: No liability is accepted for incorrect use of product.

WARRANTY: Guarantee is 12 months from purchase date, proof of which will be required for any claim.

01284 703534

Sealey Group, Kempson Way, Suffolk Business Park, Bury St Edmunds, Suffolk. IP32 7AR 

sales@sealey.co.uk

SM1308 Issue 2 PL 21/11/17