

**DM-920, DM-921 & DM-922
2,000 & 4,000 Count Digital Multimeters**



The **MDM-920 Series** digital multimeters are suitable for use by electricians, electronic engineers, general industry and laboratories. They are EN61010-1 CAT III rated with 2,000 or 4,000 counts.

- Impact-resistant rubber and ABS plastic case with a flip-out desk stand
- Single positive rotary selection
- Measuring rate of 2 times per second
- 34mm LCD display with large digits
- Auto Polarity indication
- Fast Blow Fuse for overload protection
- Low Battery indication
- Supplied with soft zip carry pouch, 2 test leads and battery
- Supplied with K-Type temperature bead probe (**MDM-921 & MDM-922**)

MDM-920 Additional Features:

- Manual Ranging 2,000 counts

MDM-921 Additional Features:

- Auto Ranging 2,000 counts
- Range Hold with Over Range indication
- Data Hold
- Max Hold
- Auto Power Off
- Temperature

MDM-922 Additional Features

- Auto Ranging 4,000 counts
- Range Hold with over range indication
- Data Hold
- Relative mode
- Auto Power Off
- Temperature

Technical Specifications

Function	Range	Basic Accuracy	MDM-		
			920	921	922
DC Voltage	600V	±0.5%	*	*	*
AC Voltage	600V	±1.2%	*	*	*
DC Current	10A	±2.5%	*	*	*
AC Current	10A	±3%		*	*
Resistance		±0.8%	2MΩ	20MΩ	40MΩ
Capacitance	200μF	±3.0%			*
Frequency	10MHz	±1.5%			*
Temperature	760°C, 1,400°F	±3%		*	*
Diode Check	Open circuit voltage 2.8V DC typical; test current 1mA		*	*	*
Continuity	Threshold 30Ω		*	*	*
Dimensions	150 x 70 x 48mm				
Weight	255g				