

# FGL-600

## 600g x 0.01g Precision Weighing Balance



### PRODUCT DESCRIPTION

This precision weighing balance is housed in an impact-resistant ABS case with a 115mm stainless steel weighing pan, splash-proof membrane keypad, levelling bubble and adjustable feet. The balance can be either battery or mains powered via an AC/DC Adaptor.

- Weighs in g, oz, ct & tola
- Impact-resistant ABS case with adjustable feet
- Splash-proof membrane keypad incorporating 3 function keys
- 115mmØ Stainless Steel weighing pan
- 26mm Hi-Contrast LCD display with Backlight
- Automatic backlight when weight is placed on the pan
- Zero tracking ensures stable and repeatable readings
- Tare facility over the full range
- Overload protection to 100% over capacity
- Low Battery indication
- Auto Power Off after 1.5 minutes of no activity (battery powered only)
- Supplied with user guide and battery
- 2 year warranty

### TECHNICAL SPECIFICATION

<b>Capacity</b>	600g
<b>Resolution</b>	0.01g
<b>Accuracy</b>	±0.02g
<b>Power</b>	4 x 1.5V AA Alkaline Battery ( <b>ALR-6</b> ) or AC/DC Mains Power Adaptor ( <b>APW-100</b> )
<b>Dimensions</b>	230 x 180 x 60mm (Unit) 115mmØ (Pan)
<b>Weight</b>	1.5Kg

### CALIBRATION INFORMATION

**Calibration Certificate**

**Issued at 5 points:**

100g, 200g, 300g, 400g & 500g

**Additional points at:**

£10.00 per point