

Product Specification PDF

Date	Correct as of 15th May 2019
Brand	C.K
Product	T3008
Description	High Speed Steel Multi-Step Drill 6-30.5mm
Barcode	5013969985283
Commodity code	8207506000
Country of origin	CN



Features & Benefits

~ Centres, drills and deburs sheet metals in one operation ~ HSS, precision ground for accurate drilling ~ Dual flute construction for faster drilling & longer life ~ Three flats on drive shaft for secure drive in drill chucks ~ Cuts hole sizes: 6, 9, 12.5, 15.2, 18.6, 20.4, 22.5, 25.5, 28.3 & 30.5mm (PG7, PG9, PG11, PG13, PG16, M25, PG21),

Product Weights and Measures

	Product only	Product & primary packaging	Secondary packaging	Transit packaging
Item Quantity	1	1	5	120
Width mm	31	35	150	300
Depth mm	31	35	120	350
Height mm	95	115	90	300
Weight	146	191	1018	25.1
Packaging Information	Card use	0	Box	Case
	Card gms	0	63	675
	Plastic use	Tube	0	-
	Plastic gms	45	0	0
	Metal use	0	0	-
	Metal gms	0	0	0
	Timber use	0	0	-
	Timber gms	0	0	0