

# Product Specification PDF

Date	Correct as of 11th May 2020
Brand	C.K
Product	T3779D 115
Description	SensoPlus Side Cutter 125mm
Barcode	5013969982039
Commodity code	8203200000
Country of origin	DE



Features & Benefits	~ Special alloy steel, drop forged, hardened & tempered for exceptional strength & durability ~ Precision box joint construction for permanent, adjustment free jaw alignment ~ Induction hardened jaws for outstanding long term performance ~ Mirror polished surface eliminates the risk of damage from flaking chrome ~ Spot welded double leaf springs for consistent, repetitive action ~ Ergonomically designed dual component handles for increased comfort & control ~ Fully ESD compliant for safe use on sensitive electronic components ~ According to IEC 61340 5.1 & 5.2 ~ Tungsten carbide blades for extreme demands e.g. piano, nickel and diode wires that are used in electronics and aerospace industries ~ Oval head ~ Bevel: Mini-Bevel ~ Length of cutting edges: 10 mm ~ Overall length: 125 mm ~ Cutting capacities wire: Piano: 0,6 mm / Hard: 1,0 mm / Soft: 2,0 mm
Applicable Standards	IEC 61340 5.1 & 5.2
Health & Safety	None applicable
Warranty	C.K products are guaranteed for 1year against imperfect materials or workmanship. Damage caused through normal wear and tear or resulting from inappropriate use, is not covered.

## Product Weights and Measures

	Product only	Product & primary packaging	Secondary packaging	Transit packaging
Item Quantity	1	1	0	120
Width mm	75	60	0	380
Depth mm	12	25	0	300
Height mm	125	160	0	360
Weight	62	81	0	10.5
Packaging Information	Card use	Box	0	Case
	Card gms	18	0	787.5
	Plastic use	Bag	0	-
	Plastic gms	1	0	-
	Metal use	0	0	-
	Metal gms	0	0	0
	Timber use	0	0	-
	Timber gms	0	0	0