

# Product Specification PDF

Date	<b>Correct as of 11th May 2020</b>
Brand	<b>C.K</b>
Product	<b>T4358 15</b>
Description	<b>Bolt Cutter 15"/380mm</b>
Barcode	<b>5013969553406</b>
Commodity code	<b>8203400000</b>
Country of origin	<b>DE</b>



## Features & Benefits

~ For cutting round material and hard wire up to 40HRC ~ Head and cutting edges manufactured from hot drop forged Chrome vanadium steel ~ Induction hardened cutting edges, tubular handles plastic coated ~ Replacement heads are separately available ~ Cutting capacity  $\varnothing$  : 785Nmm<sup>2</sup> ~ 7 mm / 1226Nmm<sup>2</sup> ~ 6 mm ~ Overall length: 400 mm

## Product Weights and Measures

	Product only	Product & primary packaging	Secondary packaging	Transit packaging
Item Quantity	1	1	1	10
Width mm	115	0	0	300
Depth mm	25	0	0	350
Height mm	390	0	0	300
Weight	845	845	855	9.2
Packaging Information	Card use	0	0	Case
	Card gms	0	0	675
	Plastic use	0	Bag	-
	Plastic gms	0	10	0
	Metal use	0	0	-
	Metal gms	0	0	0
	Timber use	0	0	-
	Timber gms	0	0	0