

Product Specification PDF

| | |
|-------------------|------------------------------------|
| Date | Correct as of 11th May 2020 |
| Brand | C.K |
| Product | T4371A |
| Description | Bolt Cutter 10"/250mm |
| Barcode | 5013969334005 |
| Commodity code | 8203400000 |
| Country of origin | DE |



Features & Benefits

~ Compact cutters ideal for fencing, meshes and low tensile wire ~ Hot drop forged chrome vanadium steel jaws with induction hardened cutting edges for strength and durability ~ Compound action mechanism applies extreme cutting forces. ~ Cutting capacity \varnothing : 785Nmm²~ 5 mm / 1226Nmm² ~ 3 mm ~ Overall length: 250 mm

Applicable Standards

Health & Safety

None applicable

Warranty

C.K products are guaranteed for 1year against imperfect materials or workmanship. Damage caused through normal wear and tear or resulting from inappropriate use, is not covered.

Product Weights and Measures

| | Product only | Product & primary packaging | Secondary packaging | Transit packaging |
|-----------------------|--------------|-----------------------------|---------------------|-------------------|
| Item Quantity | 1 | 1 | 2 | 24 |
| Width mm | 80 | 110 | 100 | 300 |
| Depth mm | 20 | 23 | 300 | 350 |
| Height mm | 255 | 330 | 65 | 300 |
| Weight | 462 | 486 | 1040 | 13.2 |
| Packaging Information | Card use | 0 | Box | Case |
| | Card gms | 0 | 68 | 675 |
| | Plastic use | Wallet | 0 | - |
| | Plastic gms | 24 | 0 | 0 |
| | Metal use | 0 | 0 | - |
| | Metal gms | 0 | 0 | 0 |
| | Timber use | 0 | 0 | - |
| | Timber gms | 0 | 0 | 0 |