

# Product Specification PDF

Date	<b>Correct as of 6th Aug 2019</b>
Brand	<b>C.K</b>
Product	<b>T4845 09</b>
Description	<b>Xonic Ceramic Trimmer 0.9mm</b>
Barcode	<b>5013969933703</b>
Commodity code	<b>8205400000</b>
Country of origin	<b>DE</b>



## Features & Benefits

~ Zirconia ceramic tips ~ safe trimming of highly sensitive electrical components ~ No electromagnetic induction ~ No eddy current loss in HF (high frequency) ~ 100 % electric insulation ~ 100 % non-magnetic ~ 100 % non-static ~ Unequalled resistance to wear □ 10 x better than metal / 100 x better than plastic ~ Total heat resistance of blades up to 1000°C ~ Extremely low thermal conductivity ~ 100 % rustproof ~ Highly resistant to all strong acids ( other than Hydrofluoric) ~ Anti-stick surface to prevent solder, soft or silverm to adhere to surfaces ~ Contamination free blades make them suitable for clean-rooms ~ Blade width: 0,9 mm ~ Blade thickness: 0,4 mm ~ Visible blade length: 15 mm ~ Overall length: 100 mm

## Applicable Standards

### Health & Safety

None applicable

### Warranty

C.K products are guaranteed for 1year against imperfect materials or workmanship. Damage caused through normal wear and tear or resulting from inappropriate use, is not covered.

## Product Weights and Measures

	Product only	Product & primary packaging	Secondary packaging	Transit packaging
Item Quantity	1	1	10	240
Width mm	12	70	130	460
Depth mm	12	20	245	300
Height mm	110	210	70	260
Weight	6	20	285	7.6
Packaging Information	Card use	Card	Box	Case
	Card gms	6	85	787.5
	Plastic use	Blister	0	-
	Plastic gms	8	0	0
	Metal use	0	0	-
	Metal gms	0	0	0
	Timber use	0	0	-
	Timber gms	0	0	0