

Product Specification PDF

Date	Correct as of 6th Aug 2019
Brand	C.K
Product	T4845 13
Description	Xonic Ceramic Trimmer 1.3mm
Barcode	5013969881400
Commodity code	8205400000
Country of origin	DE



Features & Benefits

~ Zirconia ceramic tips ~ safe trimming of highly sensitive electrical components ~ No electromagnetic induction ~ No eddy current loss in HF (high frequency) ~ 100 % electric insulation ~ 100 % non-magnetic ~ 100 % non-static ~ Unequalled resistance to wear □ 10 x better than metal / 100 x better than plastic ~ Total heat resistance of blades up to 1000°C ~ Extremely low thermal conductivity ~ 100 % rustproof ~ Highly resistant to all strong acids (other than Hydrofluoric) ~ Anti-stick surface to prevent solder, soft or silverm to adhere to surfaces ~ Contamination free blades make them suitable for clean-rooms ~ Blade width: 1,3 mm ~ Blade thickness: 0,4 mm ~ Visible blade length: 15 mm ~ Overall length: 100 mm

Applicable Standards

Health & Safety

None applicable

Warranty

C.K products are guaranteed for 1year against imperfect materials or workmanship. Damage caused through normal wear and tear or resulting from inappropriate use, is not covered.

Product Weights and Measures

	Product only	Product & primary packaging	Secondary packaging	Transit packaging
Item Quantity	1	1	10	240
Width mm	12	70	130	460
Depth mm	12	20	245	300
Height mm	110	210	70	260
Weight	6	20	285	7.6
Packaging Information	Card use	Card	Box	Case
	Card gms	6	85	787.5
	Plastic use	Blister	0	-
	Plastic gms	8	0	0
	Metal use	0	0	-
	Metal gms	0	0	0
	Timber use	0	0	-
	Timber gms	0	0	0