

# Product Specification PDF

Date	<b>Correct as of 14th Aug 2019</b>
Brand	<b>C.K</b>
Product	<b>T4856A</b>
Description	<b>Xonic 4 In 1 Trimmer</b>
Barcode	<b>5013969966701</b>
Commodity code	<b>8205400000</b>
Country of origin	<b>DE</b>



## Features & Benefits

~ Zirconia ceramic tips ~ safe trimming of highly sensitive electrical components ~ No electromagnetic induction ~ No eddy current loss in HF (high frequency) ~ 100 % electric insulation ~ 100 % non-magnetic ~ 100 % non-static ~ Unequalled resistance to wear □ 10 x better than metal / 100 x better than plastic ~ Total heat resistance of blades up to 1000°C ~ Extremely low thermal conductivity ~ 100 % rustproof ~ Highly resistant to all strong acids ( other than Hydrofluoric) ~ Anti-stick surface to prevent solder, soft or silverm to adhere to surfaces ~ Contamination free blades make them suitable for clean-rooms ~ Screwdriver handle with 2 reversible double blade inserts ~ Blade inserts: Slotted 0,9 mm, 1,8 mm and 2,6 mm as well as PH 0 special Visible blade length: all 15 mm Overall length: 145 mm

## Applicable Standards

### Health & Safety

None applicable

### Warranty

C.K products are guaranteed for 1year against imperfect materials or workmanship. Damage caused through normal wear and tear or resulting from inappropriate use, is not covered.

## Product Weights and Measures

	Product only	Product & primary packaging	Secondary packaging	Transit packaging
Item Quantity	1	1	10	0
Width mm	12	70	130	0
Depth mm	12	20	245	0
Height mm	155	210	70	0
Weight	12	26	345	0.00
Packaging Information	Card use	Card	Box	loose
	Card gms	6	85	0
	Plastic use	Blister	0	-
	Plastic gms	8	0	0
	Metal use	0	0	-
	Metal gms	0	0	0
	Timber use	0	0	-
	Timber gms	0	0	0