Product Specification PDF



| Date | Correct as of 14th Aug 2019 | | |
|-------------------|-----------------------------|--|--|
| Brand | C.K | | |
| Product | T4877X 08 | | |
| Description | Xonic Screwdriver Torx 08 | | |
| Barcode | 5013969978735 | | |
| Commodity code | 8205400000 | | |
| Country of origin | DE | | |



Features & Benefits

 \sim Ergonomically designed handle with hollow rotating cap for ease of use & precise control \sim Premium quality chrome vanadium steel blade for exceptional strength & durability \sim Precision machined tip for an exact screw fit & damage free screwdriving \sim Black anti-peel tips eliminates the risk of damage from flaking chrome \sim Tip type colour coding for easy identification \sim Size: TX08 \sim Blade diameter: 3,5 mm \sim Visible blade length: 60 mm \sim Overeall length: 157 mm

Applicable Standards

Health & Safety None applicable

Warranty C.K products are guaranteed for 1year against imperfect materials or workmanship. Damage caused through

normal wear and tear or resulting from inappropriate use, is not covered.

| Product Weights and Measures | | | | | |
|------------------------------|--------------|-----------------------------|---------------------|-------------------|--|
| | Product only | Product & primary packaging | Secondary packaging | Transit packaging | |
| Item Quantity | 1 | 1 | 30 | 0 | |
| Width mm | 17 | 17 | 245 | 0 | |
| Depth mm | 17 | 17 | 125 | 0 | |
| Height mm | 160 | 207 | 65 | 0 | |
| Weight | 18 | 25 | 830 | 0 | |
| Packaging Information | Card use | 0 | Box | loose | |
| | Card gms | 0 | 80 | 0 | |
| | Plastic use | Hanger | 0 | - | |
| | Plastic gms | 7 | 0 | 0 | |
| | Metal use | 0 | 0 | - | |
| | Metal gms | 0 | 0 | 0 | |
| | Timber use | 0 | 0 | - | |
| | Timber gms | 0 | 0 | 0 | |