

# Product Specification PDF

Date	<b>Correct as of 14th Aug 2019</b>
Brand	<b>C.K</b>
Product	<b>T4965 12</b>
Description	<b>HDComfort Screwdriver Slotted 300x6mm</b>
Barcode	<b>5013969606102</b>
Commodity code	<b>8205400000</b>
Country of origin	<b>DE</b>



## Features & Benefits

~ Shatter resistant acetate handle ~ wipe clean, oil & acid resistant ~ Large square shape handle design for maximum torque ~ Handle injection moulded directly to blade giving the ultimate bond for increased reliability & durability ~ Anti roll flats to prevent the screwdriver rolling off sloping surfaces ~ Chrome plated toughened alloy steel blade for increased strength & durability ~ Precision machined tip for an exact screw fit & damage free screwdriving ~ Drop forged blades from Chrome Vanadium/Molybdenum steel, hardened and tempered ~ According to DIN 5264, ISO 2380-2 ~ Blade width: 6 mm ~ Visible blade length: 300 mm ~ Overall length: 400 mm

## Applicable Standards

### Health & Safety

Users and bystanders are advised to wear eye protection

### Warranty

C.K products are guaranteed for 1year against imperfect materials or workmanship. Damage caused through normal wear and tear or resulting from inappropriate use, is not covered.

## Product Weights and Measures

	Product only	Product & primary packaging	Secondary packaging	Transit packaging
Item Quantity	1	1	6	72
Width mm	27	27	110	400
Depth mm	27	27	403	300
Height mm	400	400	40	300
Weight	131	131	892	11.6
Packaging Information	Card use	0	Box	Case
	Card gms	0	106	900
	Plastic use		0	-
	Plastic gms	0	0	0
	Metal use	0	0	-
	Metal gms	0	0	0
	Timber use	0	0	-
	Timber gms	0	0	0