

# Product Specification PDF

Date	<b>Correct as of 29th Apr 2020</b>
Brand	<b>Kasp</b>
Product	<b>K11960XD</b>
Description	<b>High Sec Combi Padlock 60mm Cs</b>
Barcode	<b>5013969901795</b>
Commodity code	<b>8301100000</b>
Country of origin	<b>TW</b>



## Features & Benefits

The Kasp 119 series padlocks are amongst the most secure combination padlocks available. The weather resistant electro-plated lock body with rust free internal components and dual drainage system ensures that the Kasp 119 series is ideal for outdoor use, whilst offering the convenience of a keyless locking mechanism allowing the code to be set to a memorable number of choice. ~ Supertough Molybdenum Steel Shackle ~ closed shackle version, additional protection to resist shackle attack ~ Hardened Steel Electro-plated Lock Body ~ Double Bolted Locking Mechanism ~ Extra strength to resist torsion & pull attacks ~ 4 Dial Re-settable Combination ~ Rust Free Internal Components & Dual Drainage System ~ Size: 62 mm ~ Shackle diameter: 11 mm ~ Internal height: 30 mm

## Applicable Standards

### Health & Safety

None applicable

### Warranty

KASP padlocks are guaranteed against defects in manufacture and/or materials for 10 years. Fair wear and tear or Damage caused through inappropriate use or attempted break in is not covered.

## Product Weights and Measures

	Product only	Product & primary packaging	Secondary packaging	Transit packaging
Item Quantity	1	1	6	24
Width mm	62	117	135	360
Depth mm	35	38	320	490
Height mm	90	186	200	160
Weight	663	751	4506	18.8
Packaging Information	Card use	Backing card	Box	Case
	Card gms	25	0	787.5
	Plastic use	Blister	0	-
	Plastic gms	63	0	0
	Metal use	0	0	-
	Metal gms	0	0	0
	Timber use	0	0	-
	Timber gms	0	0	0