

Product Specification PDF

| | |
|-------------------|-------------------------------|
| Date | Correct as of 29th Apr 2020 |
| Brand | Kasp |
| Product | K12440BLAA1 |
| Description | Br Padlock 40mm Black KA24401 |
| Barcode | 5013969901702 |
| Commodity code | 8301100000 |
| Country of origin | CN |



| | |
|----------------------|--|
| Features & Benefits | <p>~ Health and safety regulations regarding the isolation of industrial power supplies demand colour coded padlocks be used in conjunction with a lock off hasp. Kasp padlocks, available in 6 colours, enables different departments or maintenance teams to operate autonomously, fulfilling health and safety obligations ~ Padlock features coloured vinyl jacket to protect paintwork from accidental damage ~ Solid brass body with coloured vinyl jacket □ maximum resistance against corrosion ~ Brass shackle ~ anti spark and added resistance to corrosion ~ Double bolted locking mechanism ~ Paracentric keyway ~ extra protection against picking ~ Supplied with 2 keys ~ Lock width: 40 mm ~ Shackle diameter: 6,4 mm ~ Internal shackle height: 21 mm ~ Keyed alike, all padlocks of this order code can be opened with the same key</p> |
| Applicable Standards | |
| Health & Safety | None applicable |
| Warranty | KASP padlocks are guaranteed against defects in manufacture and/or materials for 10 years. Fair wear and tear or Damage caused through inappropriate use or attempted break in is not covered. |

Product Weights and Measures

| | Product only | Product & primary packaging | Secondary packaging | Transit packaging |
|-----------------------|--------------|-----------------------------|---------------------|-------------------|
| Item Quantity | 1 | 1 | 12 | 144 |
| Width mm | 42 | 43 | 90 | 320 |
| Depth mm | 17 | 20 | 130 | 380 |
| Height mm | 60 | 70 | 72 | 260 |
| Weight | 131 | 137 | 1686 | 21 |
| Packaging Information | Card use | Box | Box | Case |
| | Card gms | 6 | 42 | 787.5 |
| | Plastic use | 0 | 0 | - |
| | Plastic gms | 0 | 0 | 0 |
| | Metal use | 0 | 0 | - |
| | Metal gms | 0 | 0 | 0 |
| | Timber use | 0 | 0 | - |
| | Timber gms | 0 | 0 | 0 |