

Product Specification PDF

| | |
|-------------------|---------------------------------------|
| Date | Correct as of 5th May 2020 |
| Brand | Kasp |
| Product | K13040A2 |
| Description | Laminated Padlock 40mm KA30402 |
| Barcode | 5013969900927 |
| Commodity code | 8301100000 |
| Country of origin | CN |



Features & Benefits

~ Hardened steel shackle ~ Double bolted locking mechanism ~ Zinc plated steel laminated body ~ 8 steel countersunk rivets ~ extra strength over traditional locks ~ 5 pin cylinder with anti pick mushroom pins ~ Paracentric keyway ~ Supplied with 2 keys ~ Keyed alike, all padlocks of this order code can be opened with the same key ~ Padlock width: 40 mm ~ Shackle diameter: 7,1 mm ~ Internal shackle height: 21 mm

Applicable Standards

Health & Safety

None applicable

Warranty

KASP padlocks are guaranteed against defects in manufacture and/or materials for 10 years. Fair wear and tear or Damage caused through inappropriate use or attempted break in is not covered.

Product Weights and Measures

| | Product only | Product & primary packaging | Secondary packaging | Transit packaging |
|-----------------------|--------------|-----------------------------|---------------------|-------------------|
| Item Quantity | 1 | 1 | 12 | 48 |
| Width mm | 44 | 50 | 105 | 360 |
| Depth mm | 25 | 25 | 170 | 490 |
| Height mm | 65 | 70 | 70 | 160 |
| Weight | 224 | 231 | 2824 | 12.1 |
| Packaging Information | Card use | Box | Box | Case |
| | Card gms | 7 | 52 | 787.5 |
| | Plastic use | 0 | 0 | - |
| | Plastic gms | 0 | 0 | 0 |
| | Metal use | 0 | 0 | - |
| | Metal gms | 0 | 0 | 0 |
| | Timber use | 0 | 0 | - |
| | Timber gms | 0 | 0 | 0 |