

# Product Specification PDF

Date	<b>Correct as of 5th May 2020</b>
Brand	<b>Kasp</b>
Product	<b>K13040D2</b>
Description	<b>130 Padlock 40mm Twin</b>
Barcode	<b>5013969901870</b>
Commodity code	<b>8301100000</b>
Country of origin	<b>CN</b>



## Features & Benefits

~ Hardened steel shackle ~ Double bolted locking mechanism ~ Zinc plated steel laminated body ~ 8 steel countersunk rivets ~ extra strength over traditional locks ~ 5 pin cylinder with anti pick mushroom pins ~ Paracentric keyway ~ Padlock width: 40 mm ~ Shackle diameter: 7,1 mm ~ Internal shackle height: 21 mm ~ Pack contents: 2 padlocks with 3 keys ~ Keyed alike ~ both locks can be opened with same key

## Applicable Standards

### Health & Safety

None applicable

### Warranty

KASP padlocks are guaranteed against defects in manufacture and/or materials for 10 years. Fair wear and tear or Damage caused through inappropriate use or attempted break in is not covered.

## Product Weights and Measures

	Product only	Product & primary packaging	Secondary packaging	Transit packaging
Item Quantity	1	1	6	48
Width mm	155	155	165	360
Depth mm	25	25	240	490
Height mm	170	170	85	160
Weight	150	177	1164	10.1
Packaging Information	Card use	Backing card	Box	Case
	Card gms	7	102	787.5
	Plastic use	Blister	0	-
	Plastic gms	20	0	0
	Metal use	0	0	-
	Metal gms	0	0	0
	Timber use	0	0	-
	Timber gms	0	0	0