

# Product Specification PDF

Date	<b>Correct as of 5th May 2020</b>
Brand	<b>Kasp</b>
Product	<b>K13060A1</b>
Description	<b>Laminated Padlock 60mm KA30601</b>
Barcode	<b>5013969900996</b>
Commodity code	<b>8301100000</b>
Country of origin	<b>CN</b>



## Features & Benefits

~ Hardened steel shackle ~ Double bolted locking mechanism ~ Zinc plated steel laminated body ~ 8 steel countersunk rivets ~ extra strength over traditional locks ~ 5 pin cylinder with anti pick mushroom pins ~ Paracentric keyway ~ Supplied with 2 keys ~ Keyed alike, all padlocks of this order code can be opened with the same key ~ Padlock width: 60 mm ~ Shackle diameter: 11,1 mm ~ Internal shackle height: 33 mm

## Applicable Standards

### Health & Safety

None applicable

### Warranty

KASP padlocks are guaranteed against defects in manufacture and/or materials for 10 years. Fair wear and tear or Damage caused through inappropriate use or attempted break in is not covered.

## Product Weights and Measures

	Product only	Product & primary packaging	Secondary packaging	Transit packaging
Item Quantity	1	1	6	24
Width mm	63	70	125	360
Depth mm	32	38	145	490
Height mm	93	100	100	160
Weight	608	621	3776	15.9
Packaging Information	Card use	Box	Box	Case
	Card gms	13	50	787.5
	Plastic use	0	0	-
	Plastic gms	0	0	0
	Metal use	0	0	-
	Metal gms	0	0	0
	Timber use	0	0	-
	Timber gms	0	0	0