

# Product Specification PDF

Date	<b>Correct as of 11th May 2020</b>
Brand	<b>C.K</b>
Product	<b>T3655 250</b>
Description	<b>Speedy Waterpump Plier 250mm</b>
Barcode	<b>5013969948790</b>
Commodity code	<b>8203200000</b>
Country of origin	<b>DE</b>



Features & Benefits	~ Special alloy steel, drop forged, hardened & tempered for exceptional strength & durability ~ Induction hardened jaws for outstanding long term performance ~ Slide to adjust mechanism for fast & accurate size adjustment ~ Slim head & jaws for access to confined spaces ~ According to ISO 8976 ~ Maximal capacity: 38 mm Ø ~ Overall length: 250 mm
Applicable Standards	DIN ISO 8976
Health & Safety	None applicable
Warranty	C.K products are guaranteed for 1year against imperfect materials or workmanship. Damage caused through normal wear and tear or resulting from inappropriate use, is not covered.

## Product Weights and Measures

	Product only	Product & primary packaging	Secondary packaging	Transit packaging
Item Quantity	1	1	3	36
Width mm	55	60	85	360
Depth mm	15	25	300	360
Height mm	255	310	60	250
Weight	330	344	1126	14.3
Packaging Information	Card use	0	Box	Case
	Card gms	0	94	787.5
	Plastic use	Hanger	0	-
	Plastic gms	14	0	0
	Metal use	0	0	-
	Metal gms	0	0	0
	Timber use	0	0	-
	Timber gms	0	0	0