

Product Specification PDF

| | |
|-------------------|---|
| Date | Correct as of 8th May 2020 |
| Brand | C.K |
| Product | T3202 022 |
| Description | HSS Cobalt Sheet Steel Hole Saw 22mm |
| Barcode | 5013969705010 |
| Commodity code | 8207506000 |
| Country of origin | TW |



Features & Benefits

~ Tooth configuration optimised for the fast cutting of sheet steel ~ Cuts sheet steel faster than standard hole saws ~ 8 teeth per inch for a smoother cutting action ~ Cleaner holes with no burring ~ Premium grade 8% Cobalt Alloy Steel construction for an extended working life ~ Slimline design reduces frictional heat build up and prevents tooth burn out ~ compatible with impact drills ~ E6,3 Drive System ~ flared shoulders prevent overdrilling ~ avoids damaging inner components of electrical cabinets and junction boxes

Applicable Standards

Health & Safety

Users and bystanders are advised to wear safety goggles

Warranty

C.K products are guaranteed for 1year against imperfect materials or workmanship. Damage caused through normal wear and tear or resulting from inappropriate use, is not covered.

Product Weights and Measures

| | Product only | Product & primary packaging | Secondary packaging | Transit packaging |
|-----------------------|--------------|-----------------------------|---------------------|-------------------|
| Item Quantity | 1 | 1 | 10 | 60 |
| Width mm | 25 | 70 | 170 | 220 |
| Depth mm | 25 | 25 | 180 | 375 |
| Height mm | 65 | 150 | 85 | 140 |
| Weight | 40 | 51 | 576 | 4.1 |
| Packaging Information | Card use | Card | Box | Case |
| | Card gms | 5 | 66 | 675 |
| | Plastic use | Hanger | 0 | - |
| | Plastic gms | 6 | 0 | 0 |
| | Metal use | 0 | 0 | - |
| | Metal gms | 0 | 0 | 0 |
| | Timber use | 0 | 0 | - |
| | Timber gms | 0 | 0 | 0 |