

# Product Specification PDF

Date	<b>Correct as of 8th May 2020</b>
Brand	<b>C.K</b>
Product	<b>T3202 032</b>
Description	<b>HSS Cobalt Sheet Steel Hole Saw 32mm</b>
Barcode	<b>5013969705034</b>
Commodity code	<b>8207506000</b>
Country of origin	<b>TW</b>



## Features & Benefits

~ Tooth configuration optimised for the fast cutting of sheet steel ~ Cuts sheet steel faster than standard hole saws ~ 8 teeth per inch for a smoother cutting action ~ Cleaner holes with no burring ~ Premium grade 8% Cobalt Alloy Steel construction for an extended working life ~ Slimline design reduces frictional heat build up and prevents tooth burn out ~ compatible with impact drills ~ E6,3 Drive System ~ flared shoulders prevent overdrilling ~ avoids damaging inner components of electrical cabinets and junction boxes

## Applicable Standards

### Health & Safety

Users and bystanders are advised to wear safety goggles

### Warranty

C.K products are guaranteed for 1year against imperfect materials or workmanship. Damage caused through normal wear and tear or resulting from inappropriate use, is not covered.

## Product Weights and Measures

	Product only	Product & primary packaging	Secondary packaging	Transit packaging
Item Quantity	1	1	10	50
Width mm	33	70	170	220
Depth mm	33	40	245	375
Height mm	65	150	85	140
Weight	58	69	779	4.6
Packaging Information	Card use	Card	Box	Case
	Card gms	5	89	675
	Plastic use	Hanger	0	-
	Plastic gms	6	0	0
	Metal use	0	0	-
	Metal gms	0	0	0
	Timber use	0	0	-
	Timber gms	0	0	0