

# Product Specification PDF

Date	<b>Correct as of 6th Aug 2019</b>
Brand	<b>C.K</b>
Product	<b>T3014</b>
Description	<b>High Speed Steel Cone Drill 6 - 26mm</b>
Barcode	<b>5013969978070</b>
Commodity code	<b>8207506000</b>
Country of origin	<b>DE</b>



## Features & Benefits

~ Centres, drills and deburs sheet metals in one operation ~ HSS, precision ground for accurate drilling ~ Dual flute construction for faster drilling & longer life ~ Three flats on drive shaft for secure drive in drill chucks ~ Capacity: 6 ~ 26 mm

## Applicable Standards

### Health & Safety

None applicable

### Warranty

C.K products are guaranteed for 1year against imperfect materials or workmanship. Damage caused through normal wear and tear or resulting from inappropriate use, is not covered.

## Product Weights and Measures

	Product only	Product & primary packaging	Secondary packaging	Transit packaging
Item Quantity	1	1	5	70
Width mm	26	45	150	300
Depth mm	26	45	120	350
Height mm	95	115	90	300
Weight	71	116	643	9.9
Packaging Information	Card use	0	Box	Case
	Card gms	0	63	900
	Plastic use	Tube	0	-
	Plastic gms	45	0	0
	Metal use	0	0	-
	Metal gms	0	0	0
	Timber use	0	0	-
	Timber gms	0	0	0