

# Product Specification PDF

Date	<b>Correct as of 31st May 2019</b>
Brand	<b>C.K</b>
Product	<b>T3102</b>
Description	<b>HSS Split Point Drill Bit Set/13</b>
Barcode	<b>5013969781403</b>
Commodity code	<b>8207509000</b>
Country of origin	<b>DE</b>



Features & Benefits	~ High speed steel ~ 135 degree split point design for non-wander starting ~ Flute ground for accurate results ~ Conforms to DIN338 ~ Contents: 1,5 / 2,0 / 3,0 / 3,2 / 3,5 / 4,0 / 4,5 / 4,8 / 5,0 / 5,5 / 6,0 & 6,5 mm
Applicable Standards	DIN 338
Health & Safety	Users and bystanders are advised to wear safety goggles
Warranty	C.K products are guaranteed for 1year against imperfect materials or workmanship. Damage caused through normal wear and tear or resulting from inappropriate use, is not covered.

## Product Weights and Measures

	Product only	Product & primary packaging	Secondary packaging	Transit packaging
Item Quantity	1	1	0	70
Width mm	129	129	400	300
Depth mm	77	77	300	300
Height mm	13	13	120	200
Weight	88.5	123.5	0	9.4
Packaging Information	Card use	0	0	Case
	Card gms	0	0	787.5
	Plastic use	Blister	0	-
	Plastic gms	35	0	-
	Metal use	0	0	-
	Metal gms	0	0	0
	Timber use	0	0	-
	Timber gms	0	0	0