Product Specification PDF



Date	Correct as of 31st May 2019
Brand	C.K
Product	T0840 20
Description	Sabretooth Trade Saw Universal 20in
Barcode	5013969810066
Commodity code	8202100000
Country of origin	CN



Features & Benefits The Sabretooth Trade saw offers the comfort, speed and durability typically only associated with premium prices

saws. ~ Universal tooth pitch ~ Triple ground \"turbo cut\" teeth ~ for improved cutting performance ~ Offset teeth ~ for reduced friction & greater waste removal ~ Premium Grade Steel ~ rigid, 0,85 mm SK5 steel blade for maximum power transfer ~ 45 & 90° angle guides ~ for ease of marking out ~ Dual component cushion grip handle ~ for comfort and control ~ Stay sharp, hard point teeth ~ for an extended working life ~ Size: 500 mm /

20\" ~ 7 TP

Applicable Standards

Health & Safety Users are advised to wear safety goggles and protective gloves

Warranty C.K products are guaranteed for 1 year against imperfect materials or workmanship. Damage caused through

normal wear and tear or resulting from inappropriate use, is not covered.

Product Weights and Measures					
	Product only	Product & primary packaging	Secondary packaging	Transit packaging	
Item Quantity	1	1	10	40	
Width mm	600	600	650	410	
Depth mm	37	37	200	680	
Height mm	145	145	155	340	
Weight	408	443	4907	20.8	
Packaging Information	Card use	Sleeve	Box	Case	
	Card gms	27	477	1125	
	Plastic use	Blade Cover	0	-	
	Plastic gms	8	0	0	
	Metal use	0	0	-	
	Metal gms	0	0	0	
	Timber use	0	0	-	
	Timber gms	0	0	0	