

Product Specification PDF

Date	Correct as of 31st May 2019
Brand	C.K
Product	T0840 22
Description	Sabretooth Trade Saw Universal 22in
Barcode	5013969810073
Commodity code	8202100000
Country of origin	CN



Features & Benefits

The Sabretooth Trade saw offers the comfort, speed and durability typically only associated with premium price saws. ~ Universal tooth pitch ~ Triple ground \"turbo cut\" teeth ~ for improved cutting performance ~ Offset teeth ~ for reduced friction & greater waste removal ~ Premium Grade Steel ~ rigid, 0,85 mm SK5 steel blade for maximum power transfer ~ 45 & 90° angle guides ~ for ease of marking out ~ Dual component cushion grip handle ~ for comfort and control ~ Stay sharp, hard point teeth ~ for an extended working life ~ Size: 550 mm / 22\" ~ 7 TPI

Applicable Standards

Health & Safety

Users are advised to wear safety goggles and protective gloves

Warranty

C.K products are guaranteed for 1year against imperfect materials or workmanship. Damage caused through normal wear and tear or resulting from inappropriate use, is not covered.

Product Weights and Measures

	Product only	Product & primary packaging	Secondary packaging	Transit packaging
Item Quantity	1	1	10	40
Width mm	645	645	650	410
Depth mm	37	37	200	680
Height mm	145	145	155	340
Weight	432	471	5187	21.9
Packaging Information	Card use	Sleeve	Box	Case
	Card gms	31	477	1125
	Plastic use	Blade Cover	0	-
	Plastic gms	8	0	0
	Metal use	0	0	-
	Metal gms	0	0	0
	Timber use	0	0	-
	Timber gms	0	0	0