## **Product Specification PDF**



| Date              | Correct as of 6th Aug 2019          |
|-------------------|-------------------------------------|
| Brand             | C.K                                 |
| Product           | T49244-035                          |
| Description       | DextroVDE Slim S/Driver SLP 3.5x100 |
| Barcode           | 5013969032062                       |
| Commodity code    | 8205400000                          |
| Country of origin | DE                                  |



Features & Benefits ~ A slim shafted screwdriver which provides easy access to recessed screws without the need to remove any of the

insulation  $\sim$  Slim shafted insulated blades  $\sim$  allow access to recessed screws and fixings  $\sim$  VDE approved  $\sim$  individually tested to 10,000V for safe working up to 1,000V  $\sim$  100 % German manufactured  $\sim$  quality and performance assured  $\sim$  Dual component, ergonomic handle  $\sim$  specifically designed for use by electricians  $\sim$  Premium quality Chrome Vanadium steel blades  $\sim$  Optimised grip for fingertip control and final torque down power  $\sim$  Non-roll handle design  $\sim$  Permanant tip type marking on the end of the handle  $\sim$  Precision machined tips for the ultimate screw fit and high torque output  $\sim$  Blade width: 3,5 mm  $\sim$  Visible blade length: 100 mm  $\sim$  Overall length:

195 mm

Applicable Standards EN 60900 , VDE 682/2 1, ASTM-F 1505, ISO 238 -2

Health & Safety Users are advised to regularly examine their VDE tools, Even the slightest damage can compromise the insulation

integrity and potentially expose the user to the risk of injury or even death

Warranty C.K products are guaranteed for 1 year against imperfect materials or workmanship. Damage caused through normal

wear and tear or resulting from inappropriate use, is not covered.  $% \label{eq:coverage} % \label{eq:coverag$ 

| Product Weights and Measures |              |                             |                     |                   |  |
|------------------------------|--------------|-----------------------------|---------------------|-------------------|--|
|                              | Product only | Product & primary packaging | Secondary packaging | Transit packaging |  |
| Item Quantity                | 1            | 1                           | 6                   | 180               |  |
| Width mm                     | 30           | 30                          | 85                  | 310               |  |
| Depth mm                     | 25           | 25                          | 50                  | 460               |  |
| Height mm                    | 195          | 195                         | 225                 | 260               |  |
| Weight                       | 39           | 39                          | 288                 | 9.7               |  |
| Packaging Information        | Card use     | 0                           | Box                 | Case              |  |
|                              | Card gms     | 0                           | 54                  | 1012.5            |  |
|                              | Plastic use  | 0                           | 0                   | -                 |  |
|                              | Plastic gms  | 0                           | 0                   | 0                 |  |
|                              | Metal use    | 0                           | 0                   | -                 |  |
|                              | Metal gms    | 0                           | 0                   | 0                 |  |
|                              | Timber use   | 0                           | 0                   | -                 |  |
|                              | Timber gms   | 0                           | 0                   | 0                 |  |