

# Product Specification PDF

Date	<b>Correct as of 21st Sep 2020</b>
Brand	<b>C.K</b>
Product	<b>T9613</b>
Description	<b>LED Head Torch</b>
Barcode	<b>5013969246629</b>
Commodity code	<b>8513100000</b>
Country of origin	<b>CN</b>



Features & Benefits	~ High Power Cree LED ~ 220 Lumens ~ 7 Lighting modes: High, Dimmed, Red, COB, COB & Main, COB & Low Light, COB & Red Beam ~ Battery life: High: 4hrs, Low: 9hrs, Red beam: 5hrs, COB: 9hrs, Main & COB: 135 minutes ~ Sensor mode switching ability ~ Adjustable head lamp swivels through 80° ~ Impact resistant, tested to IK05 ~ Water & dirt resistant, tested to IPX4 ~ Maximum range: 90m ~ Battery 3 x AAA (Not supplied)
Applicable Standards	CE, IPX4 WEEE, RoHS
Warranty	C.K products are guaranteed for 1year against imperfect materials or workmanship. Damage caused through normal wear and tear or resulting from inappropriate use, is not covered.

## Product Weights and Measures

	Product only	Product & primary packaging	Secondary packaging	Transit packaging
Item Quantity	1	1	10	40
Width mm	70	130	400	300
Depth mm	45	70	255	300
Height mm	70	175	145	530
Weight	72	100	1200	5.5
Packaging Information	Card use	Card	Box	carton
	Card gms	18	200	700
	Plastic use	Blister	0	-
	Plastic gms	6	0	0
	Metal use	0	0	-
	Metal gms	0	0	0
	Timber use	0	0	-
	Timber gms	0	0	0