Product Specification PDF



Date	Correct as of 21st Sep 2020		
Brand	C.K		
Product	T9613USB		
Description	USB Rechargeable LED Head Torch		
Barcode	5013969246612		
Commodity code	8513100000		
Country of origin	CN		



Features & Benefits

 \sim High Power Cree LED \sim 270 Lumens \sim 7 Lighting modes: High, Dimmed, Red, COB, COB & Main, COB & Low Light, COB & Red Beam \sim Battery life: High: 4hrs, Low: 9hrs, Red beam: 6hrs, COB: 9hrs, Main & COB: 135 minutes \sim Sensor mode switching ability \sim Adjustable head lamp swivels through 80° \sim Impact resistant, tested to IK05 \sim Water & dirt resistant, tested to IPX4 \sim Maximum range: 90 m \sim Including high performance 3.7V 1800mAh Lithium-Ion rechargeable battery, USB cable

Warranty

C.K products are guaranteed for 1year against imperfect materials or workmanship. Damage caused through normal wear and tear or resulting from inappropriate use, is not covered.

Product Weights and Measures					
	Product only	Product & primary packaging	Secondary packaging	Transit packaging	
Item Quantity	1	1	10	40	
Width mm	70	130	400	300	
Depth mm	45	72	255	300	
Height mm	70	175	145	530	
Weight	100	143	1630	7.2	
Packaging Information	Card use	Card	Box	carton	
	Card gms	18	200	700	
	Plastic use	Blister	0	-	
	Plastic gms	6	0	0	
	Metal use	0	0	-	
	Metal gms	0	0	0	
	Timber use	0	0	-	
	Timber gms	0	0	0	