



Item	Part No.	Description
1	VMSC01.01	Self Tapping Screw 4 x 16mm
2	VMSC01.02	Main Body Base
3	VMSC01.03	Cable Gland
4	VMSC01.04	Mains Cable
5	VMSC01.05	Self Tapping Screw 4 x 8mm, Stainless Steel
6	VMSC01.06	Zinc Gasket
7	VMSC01.07	Wire
8	VMSC01.08	Element Support
9	VMSC01.09	Nut M5 Stainless Steel
10	VMSC01.10	Heating Element 230V 1500W
11	VMSC01.11	Pressure Switch 4-4.5Bar
12	VMSC01.12	Locktight/ Thread Glue
13	VMSC01.13	Stainless Steel Water Tank
14	VMSC01.14	Self Tapping Screw 4 x 30mm

Item	Part No.	Description
15	VMSC01.15	Body Housing
16	VMSC01.16	Screw ST2.5 x 10 Stainless Steel
17	VMSC01.17	Clamp
18	VMSC01.18	Valve
19	VMSC01.19	Plastic Spacer
20	VMSC01.20	Spring, Stainless Steel (0.7 x 7 x 16.5)
21	VMSC01.21	Safety Cap
22	VMSC01.22	Light Cover
23	VMSC01.23	Rocker Switch
24	VMSC01.24	Fixing Plate
25	VMSC01.25	Gun Holder
26	VMSC01.26	Top Handle
27	VMSC01.27	Screw ST4 x 16 Stainless Steel
28	VMSC01.28	Pressure Gauge 0-10 Bar

**NOTE:** It is our policy to continually improve products and as such we reserve the right to alter data, specifications and component parts without prior notice. There may be alternative versions of this product, please contact us should you require this information.

**IMPORTANT:** No liability is accepted for incorrect use of product. Spare parts must be fitted by a competent person

**WARRANTY:** Guarantee is 12 months from purchase date, proof of which will be required for any claim.



Parts Information:  
Steam Cleaner 2000W 2L Tank  
Model No: VMSC01

Item	Part No.	Description
29	VMSC01.29	Fixing Plate For Gauge
30	VMSC01.30	Circlip 8.3Dia
31	VMSC01.31	Pressure Pipe, 4mm ID x 8mm OD x 210mm
32	SN4.S	Steel Nut M4 Zinc
33	VMSC01.33	Cable Tie
34	VMSC01.34	PVC Thread
35	VMSC01.35	Electrical Tape (Black
36	VMSC01.36	PVC Tube 1.5m
37	VMSC01.37	Screw 4 x 16
38	VMSC01.38	Circlip
39	VMSC01.39	Pipe 4mm ID x 8mm OD x 1.86m
40	VMSC01.40	Thermostat 155Degrees
41	VMSC01.41	Fixing Plate
42	VMSC01.42	Gasket
43	VMSC01.43	Screw M4 x 10 Stainless Steel
44	VMSC01.44	Plastic Connector
45	VMSC01.45	Tube Connection
46	VMSC01.46	Tube Connection
47	VMSC01.47	Cable Tie
53	VMSC01.53	Valve
54	VMSC01.54	O-Ring (2.5 x 12mm)
55	VMSC01.55	O-Ring (3.5 x 2mm)
56	VMSC01.56	O-Ring (16 x 1.4mm)
57	VMSC01.57	Valve Core
58	VMSC01.58	Stainless Steel Spring (10 x 4 x 2)
59	VMSC01.59	Valve
60	VMSC01.60	Stainless Steel Screw (0.8 x 6.7 x 13.5mm)
61	VMSC01.61	Screw ST3 x 12 Stainless Steel

Item	Part No.	Description
62	VMSC01.62	Pipe 8 x 4mm
63	VMSC01.63	Spring 8mm Diameter
64	VMSC01.64	Pipe
65	VMSC01.65	O-Ring (11 x 2.1mm)
66	VMSC01.66	Spring (Stainless Steel) (0.8 x 7 x 2.5)
67	VMSC01.67	Press Button
68	VMSC01.68	Trigger Lock
69	VMSC01.69	Spring (Carbon Steel) 5mm
70	VMSC01.70	Trigger Lock
71	VMSC01.71	Gun Body (Right)
72	VMSC01.72	Gun Body (Left)
73	VMSC01.73	Pipe
74	VMSC01.74	Pipe (A)
75	VMSC01.75	O-Ring (11 x 2.1mm)
76	VMSC01.76	Pipe (B)
77	VMSC01.77	Stainless Steel Spring (0.8 x 7 x 25)
78	VMSC01.78	Lock
79	VMSC01.79	O-Ring (11 x 2.1mm)
84	VMSC01.84	Wire With Fuse
85	VMSC01.85	Gasket
86	VMSC01.86	Fixed Part
87	VMSC01.87	Screw M4 x 8 Stainlees Steel
88	VMSC01.88	Wire Connection
89	VMSC01.89	Silicone Cover
90	VMSC01.90	Cable Tie
91	VMSC01.91	Wheel With Cover
92	VMSC01.92	Foot

**NOTE:** It is our policy to continually improve products and as such we reserve the right to alter data, specifications and component parts without prior notice. There may be alternative versions of this product, please contact us should you require this information.

**IMPORTANT:** No liability is accepted for incorrect use of product. Spare parts must be fitted by a competent person

**WARRANTY:** Guarantee is 12 months from purchase date, proof of which will be required for any claim.

Sealey Group, Kempson Way, Suffolk Business Park, Bury St Edmunds, Suffolk. IP32 7AR



01284 757500



01284 703534



sales@sealey.co.uk



www.sealey.co.uk