


Parts Information:

Bench Grinder Ø150mm Variable Speed **Model No: BG150WVS**



NOTE: It is our policy to continually improve products and as such we reserve the right to alter data, specifications and component parts without prior notice. IMPORTANT: No liability is accepted for incorrect use of product.

WARRANTY: Guarantee is 12 months from purchase date, proof of which will be required for any claim.

Sealey Group, Kempson Way, Suffolk Business Park, Bury St Edmunds, Suffolk. IP32 7AR



01284 757500



01284 703534



sales@sealey.co.uk





Parts Information:

Bench Grinder Ø150mm Variable Speed **Model No: BG150WVS**

Item	Part No.	Description
1	BG200WVS.01	PHILLIPS SCREW (c/w WASHER) M5x16
2	BG200WVS.02	RUBBER FOOT
3	BG150WVS.03	BASE PLATE
4	BG200WVS.04	CIRCUIT BOARD
5	BG200WVS.05	SELF TAPPING SCREW ST2.9x5
6	BG150WVS.06	CIRCUIT BOARD COVER
7	BG150WVS.07	PHILLIPS SCREW (c/w SPRING WASHER) M6x18
8	SN4.S	STEEL NUT M4 ZINC DIN934 (SINGLE)
9	BG200WVS.09	COOLANT TRAY CLIP
10	BG200WVS.10	PHILLIPS SCREW M4x8
11	BG200WVS.11	COOLANT TRAY
12	BG200WVS.12	PHILLIPS SCREW (c/w SPRING+FLAT WASHER) M4x8
13	BG150WVS.13	CAPACITOR 6uF 450V
14	BG150WVS.14	BASE
15	BG200WVS.15	STRAIN RELIEF
16	BG150WVS.16	CORD CLIP
17	BG150WVS.17	CORD CLIP PLATE
18	BG200WVS.18	PHILLIPS SCREW M4x16
19	SN4.S	STEEL NUT M4 ZINC DIN934 (SINGLE)
20	BG200WVS.20	RETAINING RING
21	BG200WVS.21	CORD & PLUG
22	BG200WVS.22	TOOTHED LOCK WASHER (D4)
23	BG200WVS.23	CORD BUSHING
24	BG200WVS.24	SPEED CONTROLLER
25	BG200WVS.25	SWITCH PLATE
26	BG200WVS.26	PHILLIPS SCREW M5x10
27	BG200WVS.27	ROTARY KNOB WASHER
28	BG150WVS.28	SCREW
29	BG200WVS.29	SPEED CONTROL KNOB
30	BG200WVS.30	SWITCH GUARD
31	BG200WVS.31	PHILLIPS SCREW M3x10
32	BG200WVS.32	SWITCH
33	BG200WVS.33	SWITCH KEY
34	BG150WVS.34	FLANGE
35	BG150/16	GRINDING STONE 150x20mm 32(13)mm BORE A36Q COARSE
36	SN12.S	STEEL NUT M12 ZINC DIN934(SINGLE)
37	BG150WVS.37	GUARD COVER, LEFT
38	BG200WVS.38	PHILLIPS SCREW (SPRING+FLAT WASHER) M5x18

Item	Part No.	Description
39	BG150WVS.39	PHILLIPS SCREW M5x145
40	BG150WVS.40	FLAT WASHER (D4)
41	BG150WVS.41	ROTOR COVER (L/S)
42	BG150WVS.42	WAVE WASHER (D35)
43	B/6202	BEARING 6202
44	BG150WVS.44	STATOR
45	BG150WVS.45	ROTOR
46	BG150WVS.46	ROTOR COVER (R/S)
47	BG200WVS.47	SENSOR
48	BG150WVS.48	PHILLIPS SCREW (c/w WASHER) M2.5x6
49	BG200WVS.49	PLATE
50	BG200WVS.50	SCREW M5x6
51	BG150WVS.51	ROTOR COVER (R/S)
52	BG200WVS.52	HEX BOLT M8x12
53	BG200WVS.53	FLAT WASHER 8mm
54	NLN5.S	NYLOC NUT M5 ZINC DIN 985 (SINGLE)
55	BG200WVS.55	EYESHIELD SUPPORT
56	BG150WVS.56	EYESHIELD
57	BG200WVS.57	HEX BOLT (c/w SPRING+FLAT WASHER) M5x10
58	BG200WVS.58	PHILLIPS SCREW M4x12
59	BG200WVS.59	SHIELD, RIGHT SIDE
60	BG150WVS.60	SCREW M6x12
61	BG200WVS.61	PHILLIPS SCREW (c/w SPRING WASHER) M5x10
62	BG150WVS.62	RIGHT GUARD
63	BG150WVS.63	WORK REST, RIGHT
64	BG200WVS.64	MOVEABLE WORK REST, RIGHT
65	SN12.S	STEEL NUT M12 ZINC DIN934(SINGLE)
66	BG200WVS.66	WORK REST LOCK KNOB
67	NLN6.S	NYLOC NUT M6 ZINC DIN 985 (SINGLE)
68	BG150WVS.68	GUARD COVER, LEFT
69	BG150WVS.69	LEFT GUARD
70	BG150/15	GRINDING STONE 150x20mm 32(13)mm BORE A60P FINE
71	BG150WVS.71	WORK REST, LEFT
72	BG200WVS.72	MOVEABLE WORK REST, LEFT
73	BG200WVS.73	FLAT WASHER (D6)
74	BG150WVS.74	SHIELD, LEFT SIDE
75	BG200WVS.75	WIRE CLIP PLATE

NOTE: It is our policy to continually improve products and as such we reserve the right to alter data, specifications and component parts without prior notice. IMPORTANT: No liability is accepted for incorrect use of product.

WARRANTY: Guarantee is 12 months from purchase date, proof of which will be required for any claim.

Sealey Group, Kempson Way, Suffolk Business Park, Bury St Edmunds, Suffolk. IP32 7AR



01284 757500



01284 703534



sales@sealey.co.uk

