



SAFETY DATA SHEET
KILROCK POWER SPRAY

Page: 1

Compilation date: 27/06/2013

Revision No: 1

Section 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name: KILROCK POWER SPRAY

Product code: POWERSPRAY

1.2. Relevant identified uses of the substance or mixture and uses advised against

Use of substance / mixture: PC35: Washing and cleaning products (including solvent based products).

1.3. Details of the supplier of the safety data sheet

Company name: Kilrock Products Ltd

Units 1b/2b

Alma Road Ind Est

Chesham

Buckinghamshire

HP5 3HB

United Kingdom

Tel: +44 (0)1494 703900

Email: velda@kilrock.co.uk

1.4. Emergency telephone number

Emergency tel: +44 (0)1494 703900

(office hours only)

Section 2: Hazards identification

2.1. Classification of the substance or mixture

Classification under CHIP: This product has no classification under CHIP.

Classification under CLP: This product has no classification under CLP.

2.2. Label elements

Label elements: This product has no label elements.

2.3. Other hazards

PBT: This product is not identified as a PBT substance.

Section 3: Composition/information on ingredients

3.2. Mixtures

[cont...]

SAFETY DATA SHEET

KILROCK POWER SPRAY

Page: 2

Hazardous ingredients:

CITRIC ACID ANHYDROUS

EINECS	CAS	CHIP Classification	CLP Classification	Percent
201-069-1	77-92-9	Xi: R36/37/38	Acute Tox. 4: H302	1-10%

SULPHAMIC ACID

226-218-8	5329-14-6	Xi: R36/38; -: R52/53	Eye Irrit. 2: H319; Skin Irrit. 2: H315; Aquatic Chronic 3: H412	1-10%
-----------	-----------	-----------------------	---	-------

Section 4: First aid measures

4.1. Description of first aid measures

Skin contact: Wash immediately with plenty of soap and water.

Eye contact: Bathe the eye with running water for 15 minutes.

Ingestion: Wash out mouth with water.

Inhalation: Consult a doctor.

4.2. Most important symptoms and effects, both acute and delayed

Skin contact: There may be mild irritation at the site of contact.

Eye contact: There may be irritation and redness.

Ingestion: There may be irritation of the throat.

Inhalation: No symptoms.

4.3. Indication of any immediate medical attention and special treatment needed

Immediate / special treatment: Not applicable.

Section 5: Fire-fighting measures

5.1. Extinguishing media

Extinguishing media: Suitable extinguishing media for the surrounding fire should be used. Use water spray to cool containers.

5.2. Special hazards arising from the substance or mixture

Exposure hazards: In combustion emits toxic fumes.

5.3. Advice for fire-fighters

Advice for fire-fighters: Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

Section 6: Accidental release measures

[cont...]

SAFETY DATA SHEET

KILROCK POWER SPRAY

Page: 3

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions: Refer to section 8 of SDS for personal protection details. Turn leaking containers leak-side up to prevent the escape of liquid.

6.2. Environmental precautions

Environmental precautions: Do not discharge into drains or rivers. Contain the spillage using bunding.

6.3. Methods and material for containment and cleaning up

Clean-up procedures: Absorb into dry earth or sand. Transfer to a closable, labelled salvage container for disposal by an appropriate method.

6.4. Reference to other sections

Reference to other sections: Refer to section 8 of SDS. Refer to section 13 of SDS.

Section 7: Handling and storage

7.1. Precautions for safe handling

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions: Store in cool, well ventilated area. Keep container tightly closed.

7.3. Specific end use(s)

Specific end use(s): No data available.

Section 8: Exposure controls/personal protection

8.1. Control parameters

Hazardous ingredients:

CITRIC ACID ANHYDROUS

Workplace exposure limits:

Respirable dust

State	8 hour TWA	15 min. STEL	8 hour TWA	15 min. STEL
UK	-	-	10mg/m ³	4mg/m ³

8.1. DNEL/PNEC Values

DNEL / PNEC No data available.

8.2. Exposure controls

Engineering measures: Ensure there is sufficient ventilation of the area.

Respiratory protection: Respiratory protection not required.

Hand protection: PVC gloves. Rubber gloves.

Eye protection: Safety glasses. Ensure eye bath is to hand.

Skin protection: Protective clothing.

[cont...]

SAFETY DATA SHEET

KILROCK POWER SPRAY

Page: 4

Section 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

State: Liquid

Colour: Clear

Odour: Pleasant

Oxidising: Non-oxidising (by EC criteria)

Solubility in water: Miscible in all proportions

pH: 1

9.2. Other information

Other information: No data available.

Section 10: Stability and reactivity

10.1. Reactivity

Reactivity: Stable under recommended transport or storage conditions.

10.2. Chemical stability

Chemical stability: Stable under normal conditions.

10.3. Possibility of hazardous reactions

Hazardous reactions: Hazardous reactions will not occur under normal transport or storage conditions.

Decomposition may occur on exposure to conditions or materials listed below.

10.4. Conditions to avoid

Conditions to avoid: Heat.

10.5. Incompatible materials

Materials to avoid: Strong oxidising agents. Strong acids.

10.6. Hazardous decomposition products

Haz. decomp. products: In combustion emits toxic fumes.

Section 11: Toxicological information

11.1. Information on toxicological effects

Toxicity values:

Route	Species	Test	Value	Units
ORAL	RAT	LD50	>3000	mg/kg

[cont...]

SAFETY DATA SHEET

KILROCK POWER SPRAY

Page: 5

Hazardous ingredients:

CITRIC ACID ANHYDROUS

ORL	MUS	LD50	5040	mg/kg
ORL	RAT	LD50	3	g/kg
SCU	RAT	LD50	5500	mg/kg

SULPHAMIC ACID

IPR	RAT	LDLO	100	mg/kg
ORL	MUS	LD50	1312	mg/kg
ORL	RAT	LD50	3160	mg/kg

Symptoms / routes of exposure

Skin contact: There may be mild irritation at the site of contact.

Eye contact: There may be irritation and redness.

Ingestion: There may be irritation of the throat.

Inhalation: No symptoms.

Section 12: Ecological information

12.1. Toxicity

Ecotoxicity values: No data available.

12.2. Persistence and degradability

Persistence and degradability: Biodegradable.

12.3. Bioaccumulative potential

Bioaccumulative potential: No bioaccumulation potential.

12.4. Mobility in soil

Mobility: Readily absorbed into soil. Soluble in water.

12.5. Results of PBT and vPvB assessment

PBT identification: This product is not identified as a PBT substance.

12.6. Other adverse effects

Other adverse effects: Negligible ecotoxicity.

Section 13: Disposal considerations

[cont...]

SAFETY DATA SHEET
KILROCK POWER SPRAY

Page: 6

13.1. Waste treatment methods

Disposal operations: Deposit into or on to land (e.g. landfill, etc.)

Disposal of packaging: Dispose of as normal industrial waste.

NB: The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

Section 14: Transport information

Transport class: This product does not require a classification for transport.

Section 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Specific regulations: Not applicable.

15.2. Chemical Safety Assessment

Chemical safety assessment: A chemical safety assessment has not been carried out for the substance or the mixture by the supplier.

Section 16: Other information

Other information

Other information: This safety data sheet is prepared in accordance with Commission Regulation (EU) No 453/2010.

* indicates text in the SDS which has changed since the last revision.

Phrases used in s.2 and 3: H302: Harmful if swallowed.

H315: Causes skin irritation.

H319: Causes serious eye irritation.

H412: Harmful to aquatic life with long lasting effects.

R36/37/38: Irritating to eyes, respiratory system and skin.

R36/38: Irritating to eyes and skin.

R36: Irritating to eyes.

R52/53: Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

Legal disclaimer: The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.