

Product information

12 74 180 SB

Automatic Stripping Pliers



WW

Effortless stripping: for multi-core cables with uneven cross-section

- For control and sensor cables / actuator cables, also for stripping flexible feeding and extension cables
- Automatic adjustment to cable diameters between 4.4 mm and 7.5 mm
- No damage to the inner conductor or shield braid
- For oil-resistant, halogen-free control and sensor / actuator cables with multicore cable design
- Suitable for highly flexible TPE-U-pipes, PUR and PVC cable sheathing, rubber leads such as H05 etc.
- Long stripping lengths possible
- Body: plastic, fibreglass-reinforced
- Blade: special tool steel, oil-hardened

General	
Article No.	12 74 180 SB
EAN	4003773082323
weight	145 g
Dimensions	175 x 80 x 28 mm
Reach	no
RohS	no

Technical details Stripping capacities (diameter) Ø 4.4 — 7.5 mm

Classification	
eCl@ss 5.1.4	21040302
ETIM 5.0	EC000163
ETIM 6.0	EC000163
proficl@ss 6.0	AAA002c003

technical change and errors excepted



Required stripping length easy to read off



KNIPEX Quality – Made in Germany







