

Product information

98 13 30

- Ergonomically optimised dual component handle for fatigue reduced work and optimum transmission of force
- Handle design prevents rolling
- Chrome vanadium molybdenum steel

Screwdriver for hexagon socket screws

IEC 60900 DIN EN 60900



⚡ 1000V ○

General	
Article No.	98 13 30
EAN	4003773026341
point	burnished
Handles	insulating multi-component handle, VDE-tested
weight	49 g
Dimensions	182 x 30 x 28 mm
Standard	DIN EN 60900 IEC 60900
Reach	no
RohS	no
Technical details	
Blade length	75.0 mm
Width across flats S	3.0 mm
Length of non-insulated blade	15.0 mm
Handle length	107 mm
VDE tested	yes





Classification	
eCl@ss 5.1.4	21040401
ETIM 5.0	EC002154
ETIM 6.0	EC002154
proficl@ss 6.0	AAA889c010
UNSPSC 13.1	27111701

technical change and errors excepted