

## Product information

### 73 02 160 SB

#### KNIPEX X-Cut®

Compact Diagonal Cutter

High lever transmission

DIN ISO 5749



- Cuts finest strands as well as multi-core cables and piano wires
- Powerful, light and universal
- High cutting performance with minimum effort due to optimum coordination of the cutting edge angle and transmission ratio
- Box-joint design: highest stability with low weight
- Doubly supported joint axis for heavy duty
- Large opening width for thicker cables
- Cuts precisely, even through fine copper wires
- Compact, low-weight construction
- Universally usable, in the assembly, maintenance and production
- 40% less force required compared with standard diagonal cutters of the same length
- Chrome vanadium heavy-duty steel, forged, multi stage oil-hardened



#### General

Article No.	73 02 160 SB
EAN	4003773075349
Pliers	black atramentized
Head	polished
Handles	with multi-component grips
weight	195 g
Dimensions	160 x 85 x 20 mm
Standard	DIN ISO 5749
Reach	no
RohS	no

#### Technical details

Cutting capacities soft wire (diameter)	Ø 4.8 mm
Cutting capacities medium hard wire (diameter)	Ø 3.8 mm
Cutting capacities hard wire (diameter)	Ø 2.7 mm
Cutting capacities piano wire (diameter)	Ø 2.2 mm
Cutting capacity copper cable, multiple-stranded	Ø 12.0 mm

#### Classification

eCl@ss 5.1.4	21040302
ETIM 5.0	EC000165
ETIM 6.0	EC000165
proficl@ss 6.0	AAA949c004
UNSPSC 13.1	27112114

technical change and errors excepted

