

TS 254 M (610254380) Table saw

Order No. 610254380
EAN 4061792180352



Representative picture



- Compact mobile table saw with impressive cutting performance and high comfort for working
- Anti-twist tubular frame construction for highest demands on the building site and during installations
- Cables and all add-on components for transport can be stored on the casing
- Powerful motor with electronic overload protection
- Motor brake for quick stop of the saw blade in 3 seconds
- Restart protection: prevents unintentional start-up after power supply interruption
- Soft start for long service life of motor and drive
- Precisely adjustable parallel guide / rip fence with double clamping and quick fastening
- Precise saw blade inclination via gear guide
- Automatic resetting to 0 – 45 ° after undercuts
- Easy saw blade change with spindle lock
- Splitting wedge can be countersunk without tools for transport
- Precise, extendable table width extension for extra large working surfaces

Technical values

KEY FIGURES

Dimensions	669 x 748 x 334 mm
Working height	334 mm
Cutting height	0 - 80 mm
Maximum cutting height 90/45°	80 / 48 mm

Maximum cutting width at rip fence	520 mm
Maximum material width at mitre fence	195 mm
No-load speed	4200 rpm
Cutting speed	56 m/s
Saw blade	254 x 30 mm
Saw blade swivel range	-1.5 - 46.5 °
Rated input power S1 100%	1500 W
Weight	24.4 kg

NOISE EMISSION

Sound pressure level	92 dB(A)
Sound power level (LwA)	105 dB(A)
Uncertainty of measurement K	3 dB(A)

Scope of delivery

- Carbide saw blade with alternately bevel-ground tips (40 teeth)
- Rip Fence
- Mitre Fence
- Table Length Extension
- Table width extension (right)
- Push stick