





Position	Amount	Type number	Description	PG
1	1	315417860	Table insert	23
2	1	316052410	Table insert compl.	24
3	1	316052420	BLADE COLLAR	19
4	1	316072200	Wheel guard compl.	25
5	1	343412470	Switch cpl.	13
6	1	316071560	Table side extension compl.	35
7	1	316099840	rear table compl.	22
8	1	316071860	Parallel guide compl.	37
9	1	316072210	Angular guide compl.	31
10	1	316097110	Riving knife compl.	28
11	1	316071870	HEIGHT-ADJUSTMENT	24
12	1	343455180	Saw blade cover lower	24
13	1	316072220	Spindle stop compl.	15
14	1	316072230	Handwheel compl.	25
15	1	344114750	Rubber foot left/right cpl.	14
16	1	344114760	Foot left cpl.	17
17	1	344114770	Foot right cpl.	14
18	1	316099320	Table compl.	49
19	1	341167300	saw bracket guidance cpl.	19
20	1	343452620	Cable Big Holder	12
21	1	343452630	CABLE CLAMP cpl.	11
22	1	343452640	frame cpl.	35
23	1	316099330	Saw blade depot cpl.	19
24	1	315420670	Saw housing cpl.	33
25	1	344114780	front housing vollst.	31
26	1	316099340	Angular guide compl.	21
27	1	316099350	TERMINAL BOX cpl.	15
28	1	316099360	rear housing cpl.	21
29	1	316099370	Motor compl.	53
30	1	141112230	Countersunk screw	11
31	1	320054720	Ball bearing	15
32	1	341006750	Flange compl.	33
33	1	320050750	Ball bearing	15
34	1	143113860	Ball bearing, 12x28x8	23
35	1	343013610	Carbon Brush	14
36	1	343088140	soft start compl	15
37	1	338078800	rating plate 10254380 TS 254 M	12
38	1	342024620	Spacer	11
39	1	344114790	Rubber bushing	11
40	1	6400009900	RETAINING RING FOR SHAFTS 16X1	11
41	1	344532680	Cable with plug	26
42	1	343433180	Push stick	15
43	1	341210480	Key	13
44	1	331054770	rip fence storage	19
45	1	316075160	Scale	19
55	1	8050734103	Condenser	11
57	1	344113800	CHIP GUIDE	13
58	1	316078380	Exhaust nozzle compl.	14
1001	1	338510600	Diagram	