HSS-G plastic carry case SP, 19 pieces (627668000)

Order No. 627668000
EAN 4007430332356



Representative picture

- HSS-G Metal drill bits, ground version, cylindrical, DIN 338, type N, 135° crosswise grinding, blank surface, 19 pieces, in plastic carry case
- Ø 1 - 10 x 0.5 mm; Suitable for drilling steel and cast steel, alloyed and unalloyed, grey cast iron, malleable cast iron, ductile cast iron, sintered iron, nickel silver, graphite, non-ferrous metals, plastic; Up to 900 N/mm^2 tensile strength.
- 19-piece set, in a high-quality, robust plastic case in a special Metabo design with a Euro-hole hanger
- Ø 1 – 10 × 0.5 mm; Suitable for drilling holes in steel and cast steel (alloyed and unalloyed), grey cast iron, malleable cast iron, ductile cast iron, sintered iron, nickel silver, graphite, non-ferrous metals and plastics; Tensile strength up to 900 N/mm^2