

30m Reel 10 Way Rainbow Ribbon Cable

Order code: **01-0369**



Notes:



Colour: Multi colour
Insulation: Multi colour

Specification:

Rating: 300V 1A
Conductor size: 28awg
Insulation resistance: 100mΩ/km min.
Dielectric withstanding voltage: 1000 VAC 1 minute
Temperature range: -20°C to +80°C

Application:

Internal wiring of computers, electronic exchanges, measurement control devices, business machines, communication devices and other electronic equipment.



Pin look up table			
Pin	Cable colour	Pin	Cable colour
1	Brown	6	Blue
2	Red	7	Purple
3	Orange	8	Gray
4	Yellow	9	White
5	Green	10	Black

