


Product code: RGW-932**Construction:**

Multi-construction:

Conductor:	Bare Copper
Construction:	0.25±0.008x7
Standard Dia. (mm):	0.76
Insulation:	PVC
Thickness (mm):	0.5
Insulation Dia. (±0.1mm):	1.8x2
Insulation Colour:	White
Marking:	One black strip on one leg of twin
Print marking:	2-core 7/0.25 60 V PVC [MM] {WkYr}
Packaging:	100m cardboard reel

**Electrical Characteristics:**

Max. Conductor DC Resistance at 20°C(Ω /Km)	<55.2
Min. Insulation DC Resistance at 20°C(MΩ *Km)	200
Rated Temperature (°C)	80
Rated Voltage (V)	60

