



Product code: RGW-933**Construction:**

Multi-construction:

Conductor:	Tinned Copper
Construction:	T0.2±0.008x13
Standard Dia. (mm):	0.83
Insulation:	PVC
Thickness (mm):	0.57
Insulation Dia. (±0.1mm):	2.0x2
Insulation Colour:	Grey
Marking:	One black strip on one leg of twin
Packaging:	100m cardboard reel

**Electrical Characteristics:**

Max.Conductor DC Resistance at 20°C(Ω /Km)	<46.4
Min.Insulation DC Resistance at 20°C(MΩ *Km)	200
Rated Temperature (°C)	80
Rated Voltage (V)	60

