



DYMO® D1 Label Guide

Created specifically for your LabelManager™ label maker, D1 labels offer the performance and variety you need for any labelling job – indoor or outdoor, in your office, your workshop, your store or anywhere else you work. All DYMO® D1 labels have an “Easy Peel” back-slit for trouble-free application.



Water Resistant
Withstands water, oils, greases and most milder solvents



Temperature
Can withstand temperatures from -18°C to 90°C



Removable
Labels can be removed without leaving adhesive residue (Standard and Flexible labels only)



Easy Peel
Remove backing easily for quick and simple application



UV Resistant
Withstands exposure to sunlight without fading or peeling



Standard Polyester

For hundreds of tasks around the office or home office, such as filing, storage and asset management. Available in 6 mm, 9 mm, 12 mm, 19 mm and 24 mm x 7 m

	ABC	ABC	ABC	ABC	ABC	ABC
6 mm	S0720780	-	S0720790	-	-	-
9 mm	S0720680	S0720700	S0720730	S0720720	S0720710	S0720740
12 mm	S0720530	S0720550	S0720580	S0720570	S0720560	S0720590
19 mm	S0720830	S0720850	S0720880	S0720870	S0720860	S0720890
24 mm	S0720930	S0720950	S0720980	S0720970	S0720960	S0720990

	ABC	ABC	ABC	ABC	ABC	ABC
6 mm	S0720770	-	-	-	-	-
9 mm	S0720670	-	S0720690	-	-	-
12 mm	S0720500	S0720520	S0720540	S0720610	S0720600	S0720510
19 mm	S0720820	-	S0720840	S0720910	S0720900	-
24 mm	S0720920	-	S0720940	S0721010	S0721000	-



Permanent Polyester

For surfaces that demand a permanent solution. Available in 12 mm and 19 mm x 5,5 m

	ABC
12 mm	S0718060
19 mm	S0718070



Flexible Nylon

For curved or heavily textured surfaces. Available in 12 mm and 19 mm x 5,5 m

	ABC
12 mm	S0718040
19 mm	S0718050