

STAEDTLER® triplus® color



ERGONOMIC SHAPE FOR FATIGUE-FREE WRITING

Type:	Fibre-tip pen with ink reservoir		
Features:	Ergonomic triangular barrel for effortless and fatigue-free writing Ink washes out of most textiles easily Sturdy pressure-resistant tip DRY SAFE INK: can be left uncapped for days without drying up (Test ISO 554)		
Field of application:	Office, private, school		
Writing medium:	Paper		
Ink:	Water based dyestuff-ink, acid free, washable from many textiles		
Drying time:	Few seconds		
Cap-off time:	Several days		
Barrel:	PP		
Cap:	PP		
Tip:	Fibre tip		
Line width:	approx. 1,0 mm		
Write-out length:	approx. 500 m		
Logistical-data:			
Article-No.	Colour	Product barcode	Packaging barcode
323-1	yellow	40 07817 323021	40 07817 322581
323-16	gold ochre	40 07817 322116	40 07817 322666
323-2	red	40 07817 323052	40 07817 323762
323-20	magenta	40 07817 323120	40 07817 323724
323-23	bordeaux-red	40 07817 322123	40 07817 322673
323-3	blue	40 07817 323243	40 07817 322543
323-30	light blue	40 07817 322031	40 07817 322529
323-33	cobalt blue	40 07817 323311	40 07817 322703
323-35	turquoise	40 07817 323236	40 07817 322635
323-4	orange	40 07817 322024	40 07817 323434
323-5	green	40 07817 323045	40 07817 323465
323-50	yellow-green	40 07817 323151	40 07817 322451
323-52	sap-green	40 07817 323250	40 07817 322512
323-57	olive-green	40 07817 323267	40 07817 322567
323-6	violet	40 07817 323106	40 07817 322536
323-61	lilac	40 07817 322161	40 07817 322710
323-73	sienna-brown	40 07817 323137	40 07817 323717
323-76	vanDyckbrown	40 07817 323076	40 07817 322475
323-80	light grey	40 07817 323168	40 07817 323618
323-9	black	40 07817 323199	40 07817 322499
Smallest packaging unit:			
Contents:	10 pieces		
Weight:	84 g		
Dimension, l, w, h:	169; 62; 27 mm		
STAEDTLER Box:	easy to set up; easy removal of pens; sturdy box protects pens during transport		
Article-No.	Box with	Product barcode	Packaging barcode
323 SB10	10 pieces	40 07817 323175	40 07817 323755
323 SB20	20 pieces	40 07817 323182	40 07817 322468